








1. PACKAGING:TRAY.
2. ALL DEMENSIONS (IN BRACKNETS) FOR INFORMATION ONLY.



2							CONTACT PIN(LONG)	COPPER ALLOY	SOLOED DIDE: 3µm MIN. Sn OVER Ni INTERFACE SIDE: 2µm MIN. Ag OVER Ni	7
2							CONTACT PIN(SHORT)			6
2							CAVITY BLOCK(LONG)	LCP	BLACK	5
2							CAVITY BLOCK(SHORT)	LCP		4
1							SHIELDING HOUSING(COVE)	Zn ALLOY	3µm MIN. Sn OVER Ni	3
1							SHIELDING HOUSING (OUTSIDE)			2
				1	1	B	CODING HOUSING	PA10T	Black	1
				1		A			Black	
			1			D			Beige	
		1				C			Signal Blue	
	1					B			Claret Violet	
1						A			WATER BLUE	
	QUANTITY					CODE	DESCRIPTION	MATERIAL	FINISH & COLOR	ITEM NO.
-1	-2	-3	-4	-5	-6					
A	B	C	D	A	B	ASSY CODE				
B	B	B	B	B	B	REVISION				

CODINGS,STANDARD ORIENTATION			
CODING A	CODING B	CODING C	CODING D

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.5
1 PLC ±0.4
2 PLC ±0.4
3 PLC ±0.4
4 PLC ±0.4
ANGLES ±2°
FINISH -

WEIGHT
-

CUSTOMER DRAWING

DWN B.Lu 12DEC2022
CHK M.Chen 12DEC2022
APVD ZW.Zhou 12DEC2022

PRODUCT SPEC
108-160735
APPLICATION SPEC
116-160875

NAME
4P.COAX,HDR ASSY,90DEG
AMPSEAL 16

SIZE CAGE CODE DRAWING NO
A 00779 ©=2394674

RESTRICTED TO
-

TE Connectivity

SCALE 3:1 SHEET 1 OF 1 REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2394674-6](#)