




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN _____ CHK _____ APVD _____ PRODUCT SPEC _____ APPLICATION SPEC _____ WEIGHT _____		 TE Connectivity Ltd.	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± — 1. PLC ± — 2. PLC ± — 3. PLC ± — 4. PLC ± — ANGLES ± —		NAME SOCKET E2 ASSY LGA4710-2	
MATERIAL — FINISH —		SIZE A2		CAGE CODE 00779	
		DRAWING NO C-2397198		RESTRICTED TO —	
CUSTOMER DRAWING				SCALE	NTS 2 of 6
					REV A2

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



VIEW W

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm

MATERIAL  
-

TOLERANCES, UNLESS OTHERWISE SPECIFIED:

0. PLC	±	0.3
1. PLC	±	0.3
2. PLC	±	0.3
3. PLC	±	0.3
4. PLC	±	0.3
ANGLES	±	-

FINISH  
-

DWN  
-  
CHK  
-  
APVD  
-

PRODUCT SPEC  
-  
APPLICATION SPEC  
-

WEIGHT  
-


CUSTOMER DRAWING

TE Connectivity Ltd.

NAME  
SOCKET E2 ASSY  
LGA4710-2

SIZE A2	CAGE CODE 00779	DRAWING NO C-2397198	RESTRICTED TO -
SCALE NTS			SHEET 3 OF 6
REV A2			

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



POST SMT CONDITION (WITHOUT CAP)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

D

C

B


A

D


C

B


A




BALL SIDE BOARD LAND PATTERN




DETAIL Q (X6)



DETAIL P



DETAIL N(20:1)




DETAIL M(20:1)

KOZ LEGEND FOR REFERENCE:	
	ZONE 3: NO ROUTE ZONE,THOUGH ALL LAYERS
	ZONE 2: SOCKET CAVITY TO SOCKET ZONE. NO COMPONENT PLACEMENT ALLOWED 0.0mm HEIGHT RESTRICTION.
	ZONE 1: SOCKET CAVITY 1.222mm HEIGHT RESTRICTION.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	-	TE Connectivity Ltd.		
		CHK	-			
		APVD	-	NAME		
DIMENSIONS:		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		
mm				APPLICATION SPEC		
				WEIGHT		
MATERIAL		FINISH		CUSTOMER DRAWING		
				SIZE	CAGE CODE	DRAWING NO
				A2	00779	C=2397198
				SCALE	SHEET	REV
				NTS	5 of 6	A2

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



# SOCKET E HARD TRAY

THIS DRAWING IS A CONTROLLED DOCUMENT.		<div><div>DWN</div><div>CHK</div><div>APVD</div></div>		<div><div><div><div></div></div></div><div>TE</div></div> TE Connectivity Ltd.	
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME	
<div><div><div></div></div><div></div></div>		0. PLC ± ±0.5 1. PLC ± ±0.5 2. PLC ± ±0.5 3. PLC ± ±0.5 4. PLC ± ±0.5 ANGLES ± ±		PRODUCT SPEC	
MATERIAL		FINISH		APPLICATION SPEC	
-		-		WEIGHT -	
		CUSTOMER DRAWING		SIZE	CAGE CODE
				A2	00779
				DRAWING NO	
				C=2397198	
				RESTRICTED TO	
				-	
				SCALE	SHEET
				NTS	6 of 6
				REV	
				A2	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2397198-1](#)