

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ECN-24-280748;GTP	21AUG2024	TP	WH

NOTES:

ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED.

RoHS: COMPLIANT.

SPECIFICATIONS:

IMPEDANCE: 50Ω

FREQUENCY: DC to 11GHz

VSWR: <1.3

CONTACT RESISTANCE:
CENTER: <1.0 milliohms.
OUTER: <0.2 milliohms.

VOLTAGE RATING: 250 V (rms)

DIELECTRIC WITHSTANDING VOLTAGE: >1000V

INSULATION RESISTANCE: >5000mΩ

MECHANICAL CHARACTERISTICS

CENTER CONTACT RETENTION FORCE: >6 lbs

DURABILITY: >500 CYCLES.




ENVIRONMENTAL PARAMETER

TEMPERATURE RANGE: -40°C TO +125°C

THERMAL SHOCK: MIL-STD 202,METH.107,COND.B

VIBRATION: MIL-STD 202,METH.204,COND.B

SHOCK :MIL-STD 202,METH.213,COND.I




NOTES:

FINISH (PLATING THICKNESS IN MICRO-INCHES)

- 1 PASSIVATION
- 2 GOLD PL. 50u"/NICKEL PL.50u"/COPPER PL 10u"

	1	NOTE 2	Be-Cu C17300	CONTACT PIN	3
	1	NATURAL	PTFE ASTM-D-1710	INSULATOR	2
	1	NOTE 1	STAINLESS STEEL	BODY	1
	2492484-1	FINISH/PLATING	MATERIAL	DESCRIPTION	ITEM
QUANTITY PER ASSY			PARTS LIST		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TP	09AUG2024	 TE Connectivity						
		CHK TP	09AUG2024							
DIMENSIONS: mm		APVD WH	09AUG2024	NAME N JACK ST 4-HOLE FLANGE EXTENDED RECEP — —						
		PRODUCT SPEC SEE NOTES								
		APPLICATION SPEC —		SIZE A3	CAGE CODE 00779	DRAWING NO C-2492484	RESTRICTED TO —			
		WEIGHT 28.5								
MATERIAL SEE TABLE		FINISH —		CUSTOMER DRAWING				SCALE 1:1	SHEET 1 OF 1	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2492484-1](#)