



NOTES: UNLESS OTHERWISE SPECIFIED.

1 MATERIAL: GLASS REINFORCED THERMOPLASTIC RATED 94V-0. COLOR: BLUE.



67.87 [2.672]	50	609-5031	7-1437021-9
55.17 [2.172]	40	609-4031	5-1437021-3
47.55 [1.872]	34	609-3431	3-1437021-0
37.39 [1.472]	26	609-2631	1-1437021-0
34.85 [1.372]	24	609-2431	9-1437020-4
29.77 [1.172]	20	609-2031	8-1437020-4
24.69 [0.972]	16	609-1631	6-1437020-4
22.15 [0.872]	14	609-1431	4-1437020-9
17.07 [0.672]	10	609-1031	3-1437020-5
11.99 [0.472]	6	609-0631	2-1437020-1
A	NO OF POSN	T&B (REF. ONLY)	TE CONNECTIVITY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DRN S. SWAN	17FEB78
DIMENSIONS: mm [INCHES]		CHK	APVD
TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
0 PLC ± -	1 PLC ± -	PRODUCT SPEC	
2 PLC ± .01	3 PLC ± .005	APPLICATION SPEC	
4 PLC ANGLES ± 3° 0'		SIZE	CAGE CODE DRAWING NO
MATERIAL	FINISH	WEIGHT	A1 00779 C=2-1437020-1
CUSTOMER DRAWING		SCALE 10:1	SHEET 1 OF 1 REV C1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[609-2631](#)