


REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|---------------------------|-----------|-----|------|
| | B | PLATING CHANGED TO TRIBOR | 10JAN2017 | RP | PS |

| POS. | L±0.4 | PART NUMBER |
|------|--------|-------------|
| 2 | 5.08 | |
| 3 | 7.62 | |
| 4 | 10.16 | 5-966443-4 |
| 5 | 12.70 | |
| 6 | 15.24 | 5-966443-6 |
| 7 | 17.78 | |
| 8 | 20.32 | |
| 9 | 22.86 | |
| 10 | 25.40 | 6-966443-0 |
| 11 | 27.94 | |
| 12 | 30.48 | |
| 13 | 33.02 | |
| 14 | 35.56 | |
| 15 | 38.10 | |
| 16 | 40.64 | |
| 17 | 43.18 | |
| 18 | 45.72 | |
| 19 | 48.26 | |
| 20 | 50.80 | |
| 21 | 53.34 | |
| 22 | 55.88 | |
| 23 | 58.42 | |
| 24 | 60.96 | |
| 25 | 63.50 | |
| 26 | 66.04 | |
| 27 | 68.58 | |
| 28 | 71.12 | |
| 29 | 73.66 | |
| 30 | 76.20 | |
| 31 | 78.74 | |
| 32 | 81.28 | |
| 33 | 83.82 | |
| 34 | 86.36 | |
| 35 | 88.90 | |
| 36 | 91.44 | |
| 37 | 93.98 | |
| 38 | 96.52 | |
| 39 | 99.06 | |
| 40 | 101.60 | |
| 41 | 104.14 | |
| 42 | 106.68 | |
| 43 | 109.22 | |
| 44 | 111.76 | |
| 45 | 114.30 | |
| 46 | 116.84 | |
| 47 | 119.38 | |
| 48 | 121.92 | |
| 49 | 124.46 | |
| 50 | 127.00 | 9-966443-9 |



| | | | |
|------|-------------|----------|----------------|
| 2 | CONTACT PIN | CuSn | △ |
| 1 | PIN HOUSING | PBT | GREEN |
| ITEM | DESCRIPTION | MATERIAL | SURFACE/COLOUR |

REMARKS:

△ FINISH: TRIBOR®
UNDERLAYER: 2-4µm Ni-P(NICKEL-PHOSPHOROUS)
CONTACT AREA: 0.12-0.27µm Au(GOLD) BY AREA "F"
SOLDER TYNES: 3-5µm Sn(MATTE TIN)


2. PERMEABILITY $\mu_R \leq 1.0005$

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
ALLGEMEINTOLERANZEN
± 0.2mm

| | |
|-----------------|-----|
| 0 PLC | ± - |
| 1 PLC | ± - |
| 2 PLC | ± - |
| 3 PLC | ± - |
| 4 PLC | ± - |
| ANGLES / WINKEL | ± - |



DWN 17.02.94
F.RIECHARDT

CHK 17.02.94
M.SCHAARSCHMIDT

APVD -

PRODUCT SPEC
PRODUKTSPEZ.

APPLICATION SPEC

-

WEIGHT
GEWICHT

CUSTOMER DRAWING

MATERIAL

-

FINISH

OBERFLAECH/FARBE

-



TE Connectivity

NAME

AMPMODU II, PIN HEADER
SINGLE ROW, NON MAGNETIC

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A4

00779

C-966443

-

SCALE

1:1

SHEET
BLATT

1

OF
VON

1

REV

B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-966443-4](#)