

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES (TE). IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN TE PERSONNEL WITHOUT AUTHORIZATION FROM TE (www.te.com).

DRAWING NUMBER:
455494-ENV

B

C

D

E

F

1

2

3

4

5

6

7

8

A

B

C

D

E

F

2. NICKEL PLATED BRASS CRIMP SLEEVE

OPTICAL CONTACT ASSEMBLY INCLUDING
CERAMIC FERRULE AND ARCAP/CW400J BODY

NOTES:

1. TERMINI TO BE FITTED WITH DUST CAP AND PACKED IN A BAG MARKED WITH A MINIMUM OF THE PART NUMBER AND ITEM DESCRIPTION

2. CRIMP SLEEVE NOT SUPPLIED FOR BUFFERED FIBRE -00 VARIANT

3. FOR REFERENCE: CRIMP TOOL A/F SIZES

FOR CRIMP SIZE 00: 1.64/1.74mm
FOR CRIMP SIZE 00, 01, 02, 04: 3.02/3.10mm
FOR CRIMP SIZE 03: 3.48/3.56mm

4. EXAMPLE OF PART NUMBER: 455494 - 127 - 00

BASIC PART NUMBER

CABLE DIAMETER:

BORE SIZE ØA NOM:

00: 900µm PLAIN BUFFERED FIBRE
01: 2.50mm
02: 1.80mm
03: 3.00mm
04: 2.10mm

126 176
127 223
128 232
141 267
145 274
162 283
305

AA	DUK-71517	MJH	NPO	MJH	CP	15/04/2020
ISSUE	CHANGE NOTE	DRAWN	CHECKED	APP. ENG.	APP. MARKETING	DATE

1

2

3

4

5

6

7

8

BS8888 THIRD ANGLE PROJECTION 	MATERIAL:		FINISH:		 DEUTSCH TE CONNECTIVITY UK LTD., ST. LEONARDS-ON-SEA, TN38 9RF, UK.	
UNLESS OTHERWISE STATED: DIMENSIONS: mm [INCHES]	TITLE: MC3, OPTICAL CONTACT ASSEMBLY, RIGID,		TYPE: CUSTOMER DRAWING			
IF IN DOUBT, ASK	SIZE: A3	SCALE: 2:1	DRAWING NUMBER: 455494-ENV		SHEET: 1 OF 1	ISSUE: AA

1

2

3

4

5

6

7

8

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[455494-127-04](#)