




P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER E.O. P21520	12-8-12	DM	DM
	C1	REVISED PER E-21-000810	20JAN2021	MR	IG
	C2	REVISED PER PCN-22-147469	26JUL2022	JT	IG
	C3	REVISED PER PCN-24-202455	19ABR2024	JT	CB



- SEE SHEET 2 FOR OTHER KEY ARRANGEMENTS.
- MATERIAL: RECEPTACLE: PA66 GF; SEAL/GROMMET: VMQ; THREADED INSERT: STEEL.
- WIRE ROUTER CAP IS INCLUDED WITH RECEPTACLE (-L018).
5. THIS RECEPTACLE MATES WITH DRB16-102S*E-**** PLUG (*=A,B,C,D KEYS; **** = ALL MODIFICATIONS. CONSULT FACTORY FOR MODS)
- FOR CONTACTS AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS SEE INFORMATION DRAWING 0425-015-0000.

3. ITEMS SOLD SEPARATELY: SECONDARY LOCKS: WB-51P*R AND WB-51P*L
INTERFACE FLANGE: DRBF-1*

2. DELETED.


1. DELETED.

NOTES: UNLESS OTHERWISE SPECIFIED


CONTACT SIZE	MIN. INSUL. O.D. [mm]	MAX. INSUL. O.D. [mm]	WIRE RANGE [mm ²] REF ONLY
4	.261 [6.629]	.292 [7.417]	6 AWG [13.0]
8	.135 [3.429]	.220 [5.588]	8-10 AWG [8.0-5.0]
12	.097 [2.464]	.158 [4.013]	12-14 AWG [3.0-2.0]
16	.053 [1.346]	.120 [3.048]	14-20 AWG [2.0-0.5]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. APOSTOL 13DEC2012	TE TE Connectivity	
DIMENSIONS: INCHES [mm]		CHK P. CARNAHAN 17DEC2012		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. MEYER 18DEC2012	NAME RECEP, 102 CONTACTS KEY: A,B,C,D E SEAL; COLOR: BLACK -L018 MOD DRB SERIES	
0 PLC ±		PRODUCT SPEC 108-151021	SIZE A3	
1 PLC ±		APPLICATION SPEC -	CAGE CODE 00779	
2 PLC ±		WEIGHT -	DRAWING NO C-DRB12-102PXE-L018	
3 PLC ±.025 [.64]			RESTRICTED TO -	
4 PLC ±			SCALE 2:1	
ANGLES ±30° 0' 0"			SHEET 1 OF 2	
FINISH -			REV C3	
MATERIAL		CUSTOMER DRAWING; RESTRICTED CUSTOMER		


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




DRB12-102PAE-L018
KEY: A




DRB12-102PBE-L018
KEY: B



DRB12-102PCE-L018
KEY: C



DRB12-102PDE-L018
KEY: D

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. APOSTOL 13DEC2012	 TE Connectivity						
DIMENSIONS: INCHES [mm]		CHK P. CARNAHAN 17DEC2012							
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025 [.64] 4 PLC ± ANGLES ±30° 0' 0''	APVD D. MEYER 18DEC2012	NAME RECEP, 102 CONTACTS KEY: A,B,C,D E SEAL; COLOR: BLACK -L018 MOD DRB SERIES						
		PRODUCT SPEC 108-151021							
		APPLICATION SPEC -	SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO		
		MATERIAL 	FINISH -	WEIGHT -	A3	00779		C-DRB12-102PXE-L018	
CUSTOMER DRAWING;RESTRICTED CUSTOMER			SCALE	2:1		SHEET	2 OF 2	REV	C3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[DRB12-102PBE-L018](#)