





| REVISIONS |     |                           |           |     |      |
|-----------|-----|---------------------------|-----------|-----|------|
| P         | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|           | F1  | REVISED PER ECR-24-216887 | 06AUG2024 | GH  | AK   |





| Product Size                       | 3/32            | 1/8             | 3/16            | 1/4             | 3/8              | 1/2              | 3/4              | 1               | 1—1/2           | 2                | 2—1/4            |
|------------------------------------|-----------------|-----------------|-----------------|-----------------|------------------|------------------|------------------|-----------------|-----------------|------------------|------------------|
| Minimum Sleeve Flattened Width     | 4.32<br>(.170)  | 5.84<br>(.230)  | 8.00<br>(.315)  | 10.7<br>(.420)  | 15.5<br>(.610)   | 20.4<br>(.803)   | 30.5<br>(1.200)  | 40.4<br>(1.590) | 60.3<br>(2.37)  | 80.0<br>(3.15)   | 88.9<br>(3.50)   |
| Nominal Sleeve Progression         | 12.70<br>(.500) | 12.70<br>(.500) | 12.70<br>(.500) | 16.94<br>(.667) | 25.40<br>(1.000) | 29.64<br>(1.167) | 42.34<br>(1.667) | 50.80<br>(2.00) | 71.96<br>(2.83) | 101.60<br>(4.00) | 101.60<br>(4.00) |
| "D" Minimum Supplied I.D.          | 2.36<br>(.093)  | 3.18<br>(.125)  | 4.75<br>(.187)  | 6.35<br>(.250)  | 9.53<br>(.375)   | 12.70<br>(.500)  | 19.05<br>(.750)  | 25.40<br>(1.00) | 38.10<br>(1.50) | 50.80<br>(2.00)  | 57.15<br>(2.25)  |
| "d" Maximum Recovered I.D.         | 0.79<br>(.031)  | 1.07<br>(.042)  | 1.57<br>(.062)  | 2.11<br>(.083)  | 3.18<br>(.125)   | 4.22<br>(.166)   | 6.35<br>(.250)   | 8.46<br>(.333)  | 19.05<br>(.750) | 25.40<br>(1.00)  | 19.05<br>(.750)  |
| "w" Recovered wall<br>±0.08 (.003) | 0.58<br>(.023)  | 0.58<br>(.023)  | 0.58<br>(.023)  | 0.58<br>(.023)  | 0.61<br>(.024)   | 0.61<br>(.024)   | 0.61<br>(.024)   | 0.64<br>(.025)  | 0.51<br>(.020)  | 0.64<br>(.025)   | 0.76<br>(.030)   |

DIMENSIONS IN mm (inches)



NOTE:  
1. SIDE SCORE ALSO AVAILABLE WITH S1, S2, & S3

|   |  |  |  |   |           |                     |                 |           |
|---|--|--|--|---|-----------|---------------------|-----------------|-----------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.  |  | DWN<br>AFK08NOV2013  |  | <div>TE Connectivity</div> |           |                     |                 |           |
|   |  | CHK<br>—   |  | —   |           |                     |                 |           |
| DIMENSIONS:<br>mm   |  | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:<br><br>0 PLC±—<br>1 PLC±—<br>2 PLC±—<br>3 PLC±—<br>4 PLC±—<br>ANGLES±— |  | APVD<br>—   |           | NAME                |                 |           |
|  |  |  |  | PRODUCT SPEC<br>—   |           | TMS—SCE<br>—        |                 |           |
|   |  |  |  | APPLICATION SPEC<br>—   |           | —                   |                 |           |
|   |  |  |  | SIZE  | CAGE CODE | DRAWING NO          | RESTRICTED TO   |           |
| MATERIAL<br>CROSSLINKED POLYOLEFIN  |  | FINISH<br>—  |  | WEIGHT<br>—   |           | A306090C—MCD160002— |                 |           |
| CUSTOMER DRAWING  |  |  |  |   |           | SCALE<br>1:1        | SHEET<br>1 OF 1 | REV<br>F1 |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[CB6640-000](#)