



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	29FEB2024	AN	VN

PART AS SUPPLIED



PART FULLY RECOVERED



PRODUCT DIMENSIONS

SIZES	AS SUPPLIED		AS RECOVERED							
	D MINIMUM		A MAXIMUM		B MINIMUM		C MINIMUM		E NOMINAL	
	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.
RAYRIM-NR6	0.80	0.031	0.60	0.024	0.50	0.020	3.50	0.138	1.25	0.049
RAYRIM-NR7	1.60	0.063	1.00	0.039	0.90	0.035	4.80	0.189	1.25	0.049
RAYRIM-NR8	2.50	0.098	2.00	0.079	0.90	0.035	6.60	0.260	2.25	0.089
RAYRIM-NR9	4.50	0.177	4.20	0.165	0.90	0.035	13.50	0.531	2.20	0.087
RAYRIM-NR12	5.00	0.197	3.20	0.126	0.80	0.031	6.00	0.236	1.15	0.045

PRODUCT INFORMATION


- 1 FLAME RETARDED
- 2 SECTION: HEAT-SHRINKABLE, THERMALLY STABILISED
IRRADIATED, POLYOLEFIN
ADHESIVE: RAYCHEM HOT-MELT ADHESIVE
- 3 STANDARD SUPPLIED LENGTH: 1.2 METRES
- 4 STANDARD COLOUR IS BLACK AND ALSO AVAILABLE IN WHITE
- 5 LONGITUDINAL CHANGE +1 TO -10%
- 6 "D" ONLY APPLICABLE TO UNMODIFIED 1.2 METRES LENGTH
- 7 TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED
FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING

STANDARD CUTTING TOLERANCES(mm)

CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm(inches)



MATERIAL
SEE NOTES

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±0.1
3 PLC ±0.01
4 PLC ±0.001
ANGLES ±
FINISH -

DWN 29FEB2024

AYESHABAND N

CHK 29FEB2024

BASAVARAJA D A

APVD 29FEB2024

VLADIMIR NEMEC

PRODUCT SPEC

RK-6182

APPLICATION SPEC

114-120015

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME
RAYRIM EDGING STRIP

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	RAYRIM	-

SCALE NTS SHEET 1 OF 1 REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[RAYRIM-NR8-0-SP](#)