

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	12OCT2023	AD	CW
	A1	ECR-24-208147	08MAY2024	AD	CW


NOTES:

1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: POLYMER
RATED VOLTAGE: 600V(POWER)/250V(SIGNAL)/30V(DATA)
RATED CURRENT: 20A(POWER)/10A(SIGNAL)/1.2A(DATA)
RATED IMPULSE VOLTAGE: 6kV(POWER)/4kV(SIGNAL)/0.8kV(DATA)
POLLUTION DEGREE: 3
MATING CYCLES: 500 CYCLES
CONTACT TYPE: CRIMP CONTACT
2. CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING:T20200X20XX000/T20300X20XX000)
3. ETHERNET ELEMENT CAT5 NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING:T2080142201100)
4. GROUNDING CONTACT PACKAGED SEPARATELY IN A PE BAG.

注释:

1. 技术参数:
绝缘材料: 聚合物
额定电压: 600V(电源)/250V(信号)/30V(数据)
额定电流: 20A(电源)/10A(信号)/1.2A(数据)
额定脉冲电压: 6kV(电源)/4kV(信号)/0.8kV(数据)
污染等级: 3
插拔次数: 500次
接线类型: 冷压接
2. 端子需要单独订购.
(订货号参考图面: T20200X20XX000/T20300X20XX000)
3. 以太网组件需要单独订购.
(订货号参考图面: T2080142201100)
4. 接地端子独立包装在PE袋中.

T2080142201-000	HQ-4/4/6-F	HQ 4/4/6 HYBRID FEMALE INSERT HQ 4//6混合母插
PART NUMBER 料 号	PART DESCRIPTION 描 述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 12OCT2023 Alan Dong	 TE Connectivity		
		CHK 12OCT2023 Gino Yao			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD 12OCT2023 Chris Wang	NAME HQ 4/4/6 HYBRID FEMALE INSERT		
		PRODUCT SPEC 108-137683			
	0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH	APPLICATION SPEC 114-137683	SIZE A3		
		WEIGHT 13.6 G			
MATERIAL -	-	CUSTOMER DRAWING	SCALE 3:2	SHEET 1 OF 1	REV A1

M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.2Nm
M3螺丝, 推荐锁紧力矩0.2Nm

38.7

21.2

21.2

4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T2080142201-000](#)