


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	12OCT2023	AD	CW

- NOTES:
1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: POLYMER
RATED VOLTAGE: 30V(AC/DC)
RATED CURRENT: 1.2A
RATED IMPULSE VOLTAGE: 0.8kV
POLLUTION DEGREE: 3
MATING CYCLES: 500 CYCLES
CONTACT TYPE: CRIMP CONTACT
 2. CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING:T2400012002000)
 3. ALL THE PARTS PACKAGED IN A PE BAG AS SIGNAL ITEM.

- 注释:
1. 技术参数:
绝缘材料: 聚合物
额定电压: 30V(AC/DC)
额定电流: 1.2A
额定脉冲电压: 0.8kV
污染等级: 3
插拔次数: 500次
接线类型: 冷压接
 2. 端子需要单独订购.
(订货号参考图面: T2400012002000)
 3. 所有的零件以散件的形式包装在PE袋中.



SECTION A-A

MATING VIEW - CONTACT OUTLET

TT2080142201-100

606E-C5-6P-P

606 ETHERNET ELEMENT CAT5, 6 PIN, P-TYPE
606以太网组件, 5类, 6PIN, P型

PART NUMBER

料 号

PART DESCRIPTION

描 述

THIS DRAWING IS A CONTROLLED DOCUMENT.


DWN 12OCT2023
Alan Dong
CHK 12OCT2023
Gino Yao
APVD 12OCT2023
Chris Wang

NAME
606 ETHERNET ELEMENT CAT5,
6 PIN, P-TYPE



TE Connectivity

DIMENSIONS:
mm



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

MATERIAL

-

FINISH

-

PRODUCT SPEC
108-137683

APPLICATION SPEC
114-137683

WEIGHT

4 g

SIZE

A3

CAGE CODE

00779

DRAWING NO

T2080142201100

RESTRICTED TO

-

CUSTOMER DRAWING

SCALE

2:1

SHEET

1 OF 1

REV

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T2080142201-100](#)