






P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	16OCT2023	AD	CW

NOTES:
1. TECHNICAL CHARACTERISTICS:
CONTACT MATERIAL: BRASS ALLOY.
SURFACE TREATMENT: GOLD PLATING
CONTACT RESISTANCE: $\leq 15m\Omega$
OPERATION TEMPERATURE: $-40\sim+125^{\circ}C$
DIGITAL CRIMPING TOOL:
TE PART NO.: C0-0235-000-000
LOCATOR FOR DIGITAL CRIMPING TOOL:
TE PART NO.: C0-0265-000-000

注释:
1. 技术参数:
针件材料: 铜合金
表面处理: 镀金
接触电阻: $\leq 15m\Omega$
工作温度: $-40\sim+125^{\circ}C$
数码压接工具:
TE料号: C0-0235-000-000
数码压接工具的定位器:
TE料号: C0-0265-000-000



SECTION A-A

T2400012002-000	ETH-CS-0.6	ETHERNET SOCKET CONTACT $\varnothing 0.6\text{MM}$, GOLD PLATED, CRIMP 以太网母端子 $\varnothing 0.6$, 镀金, 压接
PART NUMBER 料 号	PART DESCRIPTION 描 述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 16OCT2023 Alan Dong	 TE Connectivity		
		CHK 16OCT2023 Gino Yao			
		APVD 16OCT2023 Chris Wang			
		PRODUCT SPEC 108-137683			
DIMENSIONS: mm		APPLICATION SPEC 114-137683	NAME ETHERNET SOCKET CONTACT CALIBER 0.6MM		
		WEIGHT 0.076 g	SIZE A3	CAGE CODE 00779	DRAWING NO T2400012002000
MATERIAL -		CUSTOMER DRAWING	SCALE 10:1	SHEET 1 OF 1	RESTRICTED TO -
				REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T2400012002-000](#)