



## T2212 THERMAL TRANSFER PRINTER AND MARKERS

The T2212 is a robust entry level industrial computer-driven 300dpi thermal transfer printer. Specially designed to print on a wide range of ENTRELEC and TE Connectivity (TE) labels, cable markers and identification heat shrink sleeves. New full-color touch screen interface, with intuitive icon-based setting adjustments. Various preloaded tutorials answer commonly-asked questions without the unit having to connect to the internet. The Printer is equipped with Additional RS232 port and Flash card, USB, Ethernet and serial ports. Product and ribbon can be loaded quickly and easily, designed for a quick setup and when changing between products. For optimal print results we recommend using the T2212 Printer in conjunction with TE identification product, ribbon and WINTOTAL software.



### HIGHLY VERSATILE

- Low - medium volume, cost effective thermal transfer printer
- Suitable for printing on tubing, tags/cable markers and adhesive labels
- Small footprint, ideal for office or manufacturing location
- Accessories available and easy to fit
- 300dpi for clear print quality



### EASY TO INSTALL AND USE

- Quick start guide provided to help setup
- TE Identification Software license included when buying the kit
- Full color touchscreen enables the operator to move quickly and easily through printer setup and operations
- Help videos preloaded showing Print head cleaning, loading product and ribbon



# T2212 THERMAL TRANSFER PRINTER AND MARKERS



## Marking system & accessories

### Printer and accessories

Description	Color	Type	Part Number	Pkg piece
T2212 Thermal transfer printer		T2212-SWARE-PRINTER-E	1SET540000R0000	1
Universal external reel holder		PRINTER-UNIVERSAL-REEL-HOLDER-E	1SET540001R0000	1
Printing head		T200-PRINHEAD-E	1SET540002R0000	1
Cutter tool		T2212-PRINTER-CUTTER-E	1SET540003R0000	1
Perforator		T2212-PRINTER-PERFORATOR-E	1SET540004R0000	1
Wintotal7 dongle		WINTOTAL-7-DONGLE-E	1SET540005R0000	1
Driver roller		T200-DR4-DRIVEROLLER-E	1SET540014R0000	1

### Ribbons

Description	Width	Color	Type	Part Number	Pkg piece
Resin ribbon - premium ink	100 mm	Black ■	1966-RIBBON-E	1SET540006R0000	2
	40 mm	Black ■	1966-RIBBON-NAR-E	1SET540007R0000	5
Wax ribbon	110 mm	Black ■	TMS-RJS-RIBBON-4RPSCE-E	1SET540008R0000	2
Resin ribbon	40 mm	Black ■	2000P-RIBBON-4TT-NAR-E	1SET540009R0000	5
Wax ribbon	110 mm	White □	T300-RIBBON-WH-E	1SET540010R0000	2
Resin and wax ribbon	40 mm	White □	2000P-RIBBON-WH-NAR-E	1SET540011R0000	6
	110 mm	White □	RIB-1976-300-110-L-9-E	1SET540012R0000	2
Resin ribbon	76 mm	White □	RIB-1976-360-076-L-9-E	1SET540013R0000	5
Resin ribbon	110 mm	Black ■	RIB-1984-300-110-L-0-E	1SET540016R0000	2
Resin ribbon	110 mm	Black ■	1330-0607-10-E 1	1SET540017R0000	2



Ribbons differ depending on the environment and application surface to which they are to adhere. You can find more information in the ribbon data sheet by scanning the QR code on the left.



## Wrap around labels SBPE

Ideal for cable identification in harsh environments. Supplied with a printable area (white or colored), self-laminating for the transparent part of the label

Description	Color	Type	Part Number	External Diam. of cable (mm)	Printing surface (H x W) (mm)	Labels Length (mm)	Nb per reel	Compatible ribbon
Wrap around cable label	White □	SBPE04-0625-WH-5	1SET530100R0000	2 to 4.1	6.3 x 25.4	19.1	5000	TMS-RJS-RIBBON-4RPSCE-E 1SET540008R0000
	Yellow ■	SBPE04-0625-YL-5	1SET530101R0000					
Self-laminating Vinyl	White □	SBPE07-1225-WH-5	1SET530102R0000	4 to 7.6	12.7 x 25.4	36.5	5000	
	Yellow ■	SBPE07-1225-YL-5	1SET530103R0000					
	Blue ■	SBPE07-1225-BL-5	1SET530104R0000					
	Red ■	SBPE07-1225-RD-5	1SET530105R0000					
	Green ■	SBPE07-1225-GN-5	1SET530106R0000					
	White □	SBPE12-1925-WH-3	1SET530107R0000	6.1 to 12.1	19 x 25.4	57.2	3000	
	Yellow ■	SBPE12-1925-YL-3	1SET530108R0000					
	Blue ■	SBPE12-1925-BL-3	1SET530109R0000					
	Red ■	SBPE12-1925-RD-3	1SET530110R0000					
	Green ■	SBPE12-1925-GN-3	1SET530111R0000					
	White □	SBPE22-2525-WH-2	1SET530112R0000	8.1 to 22	25.4 x 25.4	95.3	2000	
	Yellow ■	SBPE22-2525-YL-2	1SET530113R0000					
	Blue ■	SBPE22-2525-BL-2	1SET530114R0000					
	Red ■	SBPE22-2525-RD-2	1SET530115R0000					
	Green ■	SBPE22-2525-GN-2	1SET530116R0000					
	White □	SBPE35-3825-WH-1	1SET530117R0000	12.1 to 35.9	38.1 x 25.4	150.9	1000	
	Yellow ■	SBPE35-3825-YL-1	1SET530118R0000					
	White □	SBPE48-3850-WH-07	1SET530119R0000	12.1 to 48	38.1 x 50.8	188.9	700	
	Yellow ■	SBPE48-3850-YL-07	1SET530120R0000					



**Panel labels PLE**

Replace engraved nameplates and labels that require high durability with metallic appearance.

Description	Color	Type	Part Number	Labels			Compatible ribbon
				Width (mm)	Length (mm)	Nb per reel	
Panel label High adhesivity Polyester	White	□; PLE-027015-WH-0.75	1SET530201R0000	27	15	750	RIB-1984-300-110-L-0-E 1SET540016R0000
	Silver	□; PLE-027018-GY-0.625	1SET530202R0000	27	18	625	
	White	□; PLE-027018-WH-0.625	1SET530203R0000	27	18	625	
	White	□; PLE-030008-WH-1	1SET530204R0000	30	8.8	1000	
	White	□; PLE-035009-WH-1	1SET530205R0000	35	9	1000	
	Silver	□; PLE-035018-GY-0.625	1SET530206R0000	35	18	625	
	White	□; PLE-035018-WH-0.625	1SET530207R0000	35	18	625	
	Silver	□; PLE-045015-GY-0.75	1SET530208R0000	45	15	750	
	White	□; PLE-045015-WH-0.75	1SET530209R0000	45	15	750	
	Silver	□; PLE-060030-GY-0.4	1SET530210R0000	60	30	400	
	White	□; PLE-060030-WH-0.4	1SET530211R0000	60	30	400	
	Silver	□; PLE-100050-GY-0.25	1SET530212R0000	100	50	250	
	White	□; PLE-100050-WH-0.25	1SET530213R0000	100	50	250	

**Heat shrinkable printable tubing**



Discover all the offering on our website

**Printable tags for wire and cables**



Discover all the offering on our website

**te.com**

© 2022 TE Connectivity Ltd. family of companies. All Rights Reserved.

ENTRELEC, TE Connectivity, TE connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any changes to the information contained herein without prior notice. TE Connectivity assumes only those obligations set forth in the terms and conditions for this product and shall in no event be liable for any incidental, indirect, or consequential damages arising out of the sale, resale, use, or misapplication of the product. TE expressly disclaims any implied warranties with respect to the information contained herein, including, but not limited to, implied warranties of merchantability or fitness for a particular purpose. Dimensions, specifications and/or information contained herein are for reference purposes only and are subject to change without notice. Consult TE for the latest dimensions, specifications and/or information. Users of TE Connectivity products must make their own assessment as to whether the respective product is suitable for the respective desired application.

INDUSTRIAL / T2212 THERMAL TRANSFER PRINTER AND MARKERS / BROCHURE / EN

09/22

## **BROCHURE**

TE Connectivity  
3, rue Jean Perrin  
69687 Chassieu cedex  
France  
Tel: +33 481923100

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1SET540000R0000](#)