

TE P/N	TE CD	Nanonics P/N	Part Description
8-1589671-4	1589799	JSL051PP2GXC10N	Jumper, 1 row, LCP, 51 position, plug to plug, 1 to 1, FEP ribbon cable, 10 centimeters, 1.0 captive jackscrews.
8-1589671-5	1589799	JSL051PP2GXC15N	Jumper, 1 row, LCP, 51 position, plug to plug, 1 to 1, FEP ribbon cable, 15 centimeters, 1.0 captive jackscrews.
8-1589671-6	1589799	JSL051PP2GXC17N	Jumper, 1 row, LCP, 51 position, plug to plug, 1 to 1, FEP ribbon cable, 17 centimeters, 1.0 captive jackscrews.
8-1589671-7	1589799	JSL051PP2GXC22N	Jumper, 1 row, LCP, 51 position, plug to plug, 1 to 1, FEP ribbon cable, 22 centimeters, 1.0 captive jackscrews.
8-1589671-8	1589799	JSL051PP2GXC75N	Jumper, 1 row, LCP, 51 position, plug to plug, 1 to 1, FEP ribbon cable, 75 centimeters, 1.0 captive jackscrews.
8-1589671-9	1589799	JSL051PP2GXC80N	Jumper, 1 row, LCP, 51 position, plug to plug, 1 to 1, FEP ribbon cable, 80 centimeters, 1.0 captive jackscrews.
1589672-7	1589799	JSM015PP2GX014N	Jumper, 1 row, metal, 15 position, plug to plug, 1 to 1, 30 AWG 7 strand, FEP ribbon cable, 14 inches, 1.0 captive jackscrews.
1589672-8	1589799	JSM015PP2GX018N	Jumper, 1 row, metal, 15 position, plug to plug, 1 to 1, 30 AWG 7 strand, FEP ribbon cable, 18 inches, 1.0 captive jackscrews.
2-1589672-3	1589799	JSM025PP2GX003N	Jumper, 1 row, metal, 25 position, plug to plug, 1 to 1, 30 AWG 7 strand, FEP ribbon cable, 3 inches, 1.0 captive jackscrews.
2-1589672-4	1589799	JSM025PP2GX024N	Jumper, 1 row, metal, 25 position, plug to plug, 1 to 1, 30 AWG 7 strand, FEP ribbon cable, 24 inches, 1.0 captive jackscrews.
3-1589672-7	1589799	JSM037PP2GX072N	Jumper, 1 row, metal, 37 position, plug to plug, 1 to 1, 30 AWG 7 strand, FEP ribbon cable, 72 inches, 1.0 captive jackscrews.
5-1589672-4	1589799	JSM051PP2GXC12	Jumper, 1 row, metal, 51 position, plug to plug, 1 to 1, 30 AWG 7 strand, FEP ribbon cable, 12 centimeters.
5-1589672-5	1589799	JSM051PP2GXC12N	Jumper, 1 row, metal, 51 position, plug to plug, 1 to 1, 30 AWG 7 strand, FEP ribbon cable, 12 centimeters, 1.0 captive jackscrews.
5-1589672-6	1589799	JSM051PP2GXC17N	Jumper, 1 row, metal, 51 position, plug to plug, 1 to 1, 30 AWG 7 strand, FEP ribbon cable, 17 centimeters, 1.0 captive jackscrews.
5-1589672-7	1589799	JSM051PP2GXC22N	Jumper, 1 row, metal, 51 position, plug to plug, 1 to 1, 30 AWG 7 strand, FEP ribbon cable, 22 centimeters, 1.0 captive jackscrews.
5-1589672-8	1589799	JSM051PP2GXC50N	Jumper, 1 row, metal, 51 position, plug to plug, 1 to 1, 30 AWG 7 strand, FEP ribbon cable, 50 centimeters, 1.0 captive jackscrews.
5-1589672-9	1589799	JSM051PP2GXC75N	Jumper, 1 row, metal, 51 position, plug to plug, 1 to 1, 30 AWG 7 strand, FEP ribbon cable, 75 centimeters, 1.0 captive jackscrews.
6-1589672-0	1589799	JSM051PP2GXC80N	Jumper, 1 row, metal, 51 position, plug to plug, 1 to 1, 30 AWG 7 strand, FEP ribbon cable, 80 centimeters, 1.0 captive jackscrews.
1589799-1	1589799	JSM015PP2GX006N	Jumper, 1 row, metal, 15 position, plug to plug, 1 to 1, 30 AWG 7 strand, FEP ribbon cable, 6 inches, 1.0 captive jackscrews.
1589799-2	1589799	JSM015PP2GX002N	Jumper, 1 row, metal, 15 position, plug to plug, 1 to 1, 30 AWG 7 strand, FEP ribbon cable, 2 inches, 1.0 captive jackscrews.
1589799-3	1589799	JSM015PP2GX001N	Jumper, 1 row, metal, 15 position, plug to plug, 1 to 1, 30 AWG 7 strand, FEP ribbon cable, 1 inches, 1.0 captive jackscrews.
1589799-4	1589799	JSM015PP2GX010N	Jumper, 1 row, metal, 15 position, plug to plug, 1 to 1, 30 AWG 7 strand, FEP ribbon cable, 10 inches, 1.0 captive jackscrews.
1589799-5	1589799	JSL015PP2GX010N	Jumper, 1 row, LCP, 15 position, plug to plug, 1 to 1, 30 AWG 7 strand, FEP ribbon cable, 10 inches, 1.0 captive jackscrews.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[JSM015PP2GX006N](#)