



Technical Data

number of pins 15
 temperature range -20 °C to 130 °C
 clamping range Ø 8.5 mm to Ø 10.5 mm
 protection type when connected IP 66/67

Electrical Data

power
 rated current max. 14 / 5 A*
 rated voltage 63V (AC/DC)
 rated insulation voltage (L-L) 1500 V

mating cycles 500

Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

pollution degree 3
 over voltage category III
 max. height for operation 2000 m

Material

housing zinc diecast / plastic coated
 insulation insert PBT, PA, UL 94/V0
 seals FKM
 clamp ring brass / nickel plated

Contacts (not part of product contents)

Tools (not part of product contents)

E ST A 205 NN 00 33 0003 000
E S A 205 N 00 33 0003 000



Contact Arrangement
mating view




© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH
 Bernrieder Straße 15
 94559 Niederwinkling, Deutschland
 Tel.: +49 9962 2002-0
 Fax: +49 9962 2002-70
 E-Mail: intercontec@te.com
 Web: www.intercontec.biz



Main Dimensions
Plug

*for max. wire cross-section
pay attention to the
cross-section of used contacts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[ESTA205NN00330003000](#)