


REFERENCE TE TE PART NUMBER	DESCRIPTION DESCRIPTION	DIAMETRE ISOLANT INSULATOR Ø	ØA	ØF	ØH	MATIERE MATERIAL	COULEUR COLOR	MASSE WEIGHT
1544941-1	JOINT UNIFILAIRE FILS DE 2.5 A 4 mm²	2.65 A 3.9 mm	9.40	2.60	4.90	SILICONE MVQ 50 (AUTOLUBRIFIE)	JAUNE	0.26 g
1544941-2	JOINT UNIFILAIRE FILS DE 5 A 6 mm²	3.8 A 4.5 mm	9.40	3.40	5.70	SILICONE MVQ 50 (AUTOLUBRIFIE)	ROUGE	0.28 g
1544941-3	BOUCHON	-	9.40	-	4.90	SILICONE MVQ 50	BLANC	0.5 g



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ± 0.15 1 PLC ± 0.15 2 PLC ± 0.15 3 PLC ± 0.15 4 PLC ± 0.15 ANGLES ±
MATERIAL SEE TABLE	FINISH -

DWN C. SALGADO	12JAN2015
CHK JP. PICAUD	12JAN2015
APVD J. DAHER	12JAN2015
PRODUCT SPEC	-
APPLICATION SPEC	114-15098
WEIGHT	-

TE Connectivity

NAME
JOINT UNIFILAIRE 2.8 NGPI
SINGLE WIRE SEAL 2.8 NGPI
RANGE 2.5 TO 6 SQMM

SIZE A3	CAGE CODE 00779	DRAWING NO C-1544941	RESTRICTED TO -
------------	--------------------	-------------------------	--------------------

Customer Drawing

SCALE 7:1

SHEET 1 OF 1

REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1544941-2](#)