

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

変更

P

LTR

DESCRIPTION

ECN

DATE

DWN

APVD

O

RELEASED

FJD0-0380-04

30NOV2004

J.A

S.M

-1:AS SHOWN

製品規格


- 1.材料 : ポリプロピレン 透明。
- 2.使用温度範囲 : -20℃~+105℃
- 3.適用電線 : UL1007 最大AWG18 被覆外径 ϕ 2.1
- 4.カバー開閉回数: MAX5回
- 5.セット後のヒンジ割れは機能上問題無い為許容する。
- 6.気泡は許容する。

PRODUCT SPECIFICATION


- 1.MATERIAL : POLYPROPYLENE CLEAR.
- 2.TEMPERATURE RATING : -20℃~+105℃
- 3.APPLICATION ELECTRICWIRE : UL1007 AWG18 MAX
DIAMETER OF INSULATION : ϕ 2.1.
- 4.THE NUMBER OF TIMES OF COVER OPENING
AND CLOSEING : 5 TIMES.
- 5.THE HINGE CRACK AFTER A SET IS PERMISSION.
BECAUSE THERE IS NO PROBLEM ON THE FUNCTION.
- 6.AIR BUBBLES IS PERMISSION.

1827149-1


PART NUMBER



スケール 1:1



スケール 1:1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.DIMENSIONS:
単位: 概
mmTOLERANCES UNLESS
OTHERWISE SPECIFIED:

一般公差	±0.3
0-PLC	±
1-PLC	±
2-PLC	±
3-PLC	±
4-PLC	±
ANGLES	±

MATERIAL

材料

FINISH

仕上

DWN

J.AKASAKA

30NOV2004

CHK

D.MITSUGI

30NOV2004

APVD

S.MANABE

30NOV2004

PRODUCT SPEC

製品規格

APPLICATION SPEC

取付適用規格

WEIGHT

2.0

CUSTOMER DRAWING

tyco
ElectronicsTyco Electronics AMP K.K.
Kawasaki, Japan

NAME

名称

CABLE CLAMP 10P
REC HSG DYNAMIC 3100D

SIZE

A3

CAGE CODE

00779

DRAWING NO

C=1827149

RESTRICTED TO

-

SCALE

尺度 2:1

SHEET

1

OF

1

REV

0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1827149-1](#)