



Application Tooling > Hand Crimping Tools



Tool Grade: **Premium Crimp Tooling**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **MIL Spec, TE Product Specification (114-)**
TE Certification: **Yes – Certificate Included**
Power Technology Type: **Battery, Hydraulic, Manual**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - Other
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Hydraulic, Manual
Tooling Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free







Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 277161-1 SPLICE, COPALUM, BUTT, 2/0 AL, 1/0 CU	 TE Part # 1752787-1 HYP10 8-4/0AWG 33T HEAD	 TE Part # 58422-1 HYP8 8-4/0AWG 33T HEAD	 TE Part # 277152-1 TERMINAL, COPALUM R 2/0 1/4
 TE Part # 277152-3 TERMINAL, COPALUM R 2/0 5/16	 TE Part # 277152-4 TERMINAL, COPALUM R 2/0 3/8	 TE Part # 277152-2 TERMINAL, COPALUM R 2/0 3/8	 TE Part # 55839-1 COPALUM R 2/0A 1/0C (2)3/8
 TE Part # 2102580-1 ASSY 1/0 AL COPALUM LITE DUAL HOLE 3/8	 TE Part # 2102581-1 ASSY 2/0 AL COPALUM LITE DUAL HOLE 3/8	 TE Part # 55944-1 TERM, COPALUM NARROW 2/0AL 3/8	 TE Part # 55982-1 TERM, COPALUM R 2/0 3/8 90RH





TE Part # 1958038-1
COPALUM R 2/0AL 3/8 90 DEG



TE Part # 696819-1
COPALUM,SLD,R,2/0AL BREAKAWAY

Customers Also Bought




TE Part #1616058-6
A703CD (FAA/PMA)=RELAY



TE Part #C67617-000
DWP-125-3/4-KIT3-REFILL




TE Part #2217483-2
KIT, BTLI, DOUBLE ACTION HEAD



TE Part #251913-000
D-602-0093



TE Part #2-525441-3
PLUG GAUGE, HANDTOOL



TE Part #314948-1
HYP8/10 COPALUM SEALED 4/0AWG
DIE SET



TE Part #YABC06N-17P0000000
IN-LINE RECP



TE Part #91066-4
INSERTION/EXTRACTION TOOL



TE Part #2844430-1
DIE ASSEMBLY,1/0 AWG NI



TE Part #04-1006-5045
PT5E-150-N34-UP-250-ABC-UD-M6

Documents

Datasheets & Catalog Pages

AT-Hydraulic Crimp Tooling Solutions-1654519

English

Bottoming Dies

English

Instruction Sheets

Instruction Sheet (U.S.)

English



[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[68011-1](#)