

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	AA4	REVISED PER ECR-18-005503	30MAY2018	BDA	SG




- 1 MATING CONN P/N: □-1123722-□
- 2 APPLICABLE P.C.B LAYOUT: SEE FIG. 1
- 3 APPLICABLE P.C.B THICKNESS: 1.60
- 4 SKETCHES SHOW NO PINS MISSING.

- 6 PIN: POST TIN OVER BRASS
- 7 HOUSING: PBT, 30% GLASS, UL94-V0.

- 8 ○ : WITH PIN,
X : WITHOUT PIN.

- 10 SUPERSEDED BY 1744489-2.
- 11 SUPERSEDED BY 1744489-4.
- 12 SUPERSEDED BY 1744489-5.
- 13 SUPERSEDED BY 1744489-6.
- 14 SUPERSEDED BY 1744489-7.
- 15 SUPERSEDED BY 1744489-8.
- 16 SUPERSEDED BY 1744489-9.
- 17 SUPERSEDED BY 1-1744489-0.
- 18 SUPERSEDED BY 1-1744489-1.

VALUES FOR UL 61800-5-1				
Flam	RTIe deg C	HWI	HAI	CTI
V0	130	PLC 2	PLC 4	PLC 2_UL746



2 FIG.1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N.YAMASAKI 13MAR'01	TE Connectivity		
DIMENSIONS: mm		CHK M.SHINDO 13MAR'01			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
	0 PLC ± 1 PLC ± 0.50 2 PLC ± 0.30 3 PLC ± 4 PLC ±		3.96MM PITCH ECONOMY POWER(EP) CONN HEADER ASSY		
	FINISH		RESTRICTED TO		
MATERIAL SEE TABLE		APVD Y.KASHIWA 13MAR'01 PRODUCT SPEC 108-5609 APPLICATION SPEC —	SIZE A2	CAGE CODE 00779	DRAWING NO C=1123723
		WEIGHT			
		CUSTOMER DRAWING	SCALE 5:1	SHEET 1 of 2	REV AA4

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION
© COPYRIGHT - By - ALL RIGHTS RESERVED.	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

											27.72	29.12	31.62	NATURAL	8		7-1123723-8
														GREEN		6-1123723-8	
														BLACK		5-1123723-8	
														RED		4-1123723-8	
														BLUE		3-1123723-8	
														YELLOW		2-1123723-8	
														NATURAL		1-1123723-8	
														NATURAL			7-1123723-7
											GREEN	6-1123723-7					
											BLACK	5-1123723-7					
											RED	4-1123723-7					
											BLUE	3-1123723-7					
											YELLOW	2-1123723-7					
											NATURAL	1-1123723-7					
											NATURAL		7-1123723-6				
											GREEN	6-1123723-6					
											BLACK	5-1123723-6					
											RED	4-1123723-6					
											BLUE	3-1123723-6					
											YELLOW	2-1123723-6					
											NATURAL	1-1123723-6					
											NATURAL		7-1123723-5				
											GREEN	6-1123723-5					
											BLACK	5-1123723-5					
											RED	4-1123723-5					
											BLUE	3-1123723-5					
											YELLOW	2-1123723-5					
											NATURAL	1-1123723-5					
											NATURAL		7-1123723-4				
											GREEN	6-1123723-4					
											BLACK	5-1123723-4					
											RED	4-1123723-4					
											BLUE	3-1123723-4					
											YELLOW	2-1123723-4					
											NATURAL	1-1123723-4					
											NATURAL		7-1123723-3				
											GREEN	6-1123723-3					
											BLACK	5-1123723-3					
											RED	4-1123723-3					
											BLUE	3-1123723-3					
											YELLOW	2-1123723-3					
											NATURAL	1-1123723-3					
											NATURAL		7-1123723-2				
											GREEN	6-1123723-2					
											BLACK	5-1123723-2					
											RED	4-1123723-2					
											BLUE	3-1123723-2					
											YELLOW	2-1123723-2					
											NATURAL	1-1123723-2					
1	2	3	4	5	6	7	8	9	10	11	"C"	"B"REF	"A"REF	COLOR	POS	ASS'Y P/N	
PIN POSITION											DIMENSION						

○	○	○	○	○	○	○	○	○	○	○	39.60	41.00	43.50	NATURAL	11	18	8-1123723-1	
○	○	○	○	○	○	○	○	○	○	○				GREEN		6-1123723-1		
○	○	○	○	○	○	○	○	○	○	○				BLACK		5-1123723-1		
○	○	○	○	○	○	○	○	○	○	○				RED		4-1123723-1		
○	○	○	○	○	○	○	○	○	○	○				BLUE		3-1123723-1		
○	○	○	○	○	○	○	○	○	○	○				YELLOW		2-1123723-1		
○	○	○	○	○	○	○	○	○	○	○				NATURAL		1-1123723-1		
○	○	○	○	○	○	○	○	○	○	△	35.64	37.04	39.54	NATURAL	10	17	7-1123723-0	
○	○	○	○	○	○	○	○	○	○	△				GREEN		6-1123723-0		
○	○	○	○	○	○	○	○	○	○	△				BLACK		5-1123723-0		
○	○	○	○	○	○	○	○	○	○	△				RED		4-1123723-0		
○	○	○	○	○	○	○	○	○	○	△				BLUE		3-1123723-0		
○	○	○	○	○	○	○	○	○	○	△				YELLOW		2-1123723-0		
○	○	○	○	○	○	○	○	○	○	△				NATURAL		1-1123723-0		
○	○	○	○	○	○	○	○	○	○	△	31.68	33.08	35.58	NATURAL	16	7-1123723-9		
○	X	○	○	○	X	○	○	○	○	○	39.60	41.00	43.50	NATURAL		7-1123723-1		
○	○	○	○	○	○	○	○	○	△	△	31.68	33.08	35.58	GREEN		6-1123723-9		
○	○	○	○	○	○	○	○	○	△	△				BLACK		5-1123723-9		
○	○	○	○	○	○	○	○	○	△	△				RED		4-1123723-9		
○	○	○	○	○	○	○	○	○	△	△				BLUE		3-1123723-9		
○	○	○	○	○	○	○	○	○	△	△				YELLOW		2-1123723-9		
○	○	○	○	○	○	○	○	○	△	△				NATURAL	1-1123723-9			
○	○	○	○	○	○	○	○	○	△	△								
1	2	3	4	5	6	7	8	9	10	11	"C"	"B"	REF	"A"	REF	COLOR	POS	ASS'Y P/N
PIN POSITION											DIMENSION				COLOR	POS	ASS'Y P/N	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N.YAMASAKI 13MAR'01 CHK M.SHINDO 13MAR'01 APVD Y.KASHIWA 13MAR'01		 TE Connectivity									
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 0.50 2 PLC ± 0.30 3 PLC ± 4 PLC ± ANGLES ±		NAME 3.96MM PITCH ECONOMY POWER(EP) CONN HEADER ASSY									
				SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
MATERIAL SEE TABLE		FINISH SEE TABLE		WEIGHT A2		00779		C-1123723		—			
CUSTOMER DRAWING								SCALE		SHEET		REV	
								5:1		2 of 2		AA4	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-1123723-0](#)