


C-171506


赤色被覆
RED INS.

SERATION
セレーション

(表参照) (SEE TABS)
被覆外径 INS. DIA



⑤ JIS 呼称 2-7 無し



(P/N)	(STUD)	(H DIA)	(INS. DIA)
型番	スタッド	H-J法	被覆外径
171506-1	#8	4.34	2.03~3.18
-2	#10	5.00	2.03~3.18
-3	#8	4.34	2.67~3.56
-4	#10	5.00	2.67~3.56
-5	#12	5.66	2.03~3.18
-6	特別	5.79	2.67~3.56
-7	5mm		2.3~3.18
-8	5mm	5.00	2.67~3.56

- (F) OBSOLETE
- (E) OBSOLETE
- OBSOLETE
- (E) OBSOLETE
- (F) OBSOLETE
- (F) OBSOLETE

IN CH: 2E DIMENSIONS IN MM DO NOT SCALE PRINT

E Change Applicable Body Y.O N.Y 23JAN17 F OBSOLETE Y.O N.Y 14APR17

D1 OBSOLETE (REV. 05) F.N 47 6-16-93
 D REVISED (REV. B) P-DWG 7-4-95 4/1/98
 C REVISED (REV. B) S.O 4/1/97 1/1/97
 B ADDED MARK H.S 4/1/97 8/1/95
 A REVISED (REV. B) H.S 4/1/97 7/1/97
 O 1/1/97 1/1/97

MATERIAL 有光銅
 WIRE RANGE 0.26 ~ 1.04 AWG 22-18
 TOLERANCE ±0.4
 (EXCEPT AS NOTED) ±1.0

参考図面 (CUSTOMER COPY REFERENCE ONLY)

TE TE Connectivity

CLASS

TYPE

LOC SIZE SH NO.

JAC-171506 F

4 LTR 変更 (REVISION RECORD) DR CHK DATE

DR S. H. 1/1/97
 CHK S. H. 1/1/97

9孔型端子 RING TERMINAL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[171506-8](#)