



DETAIL A
SCALE 10:1

ENVIRONMENTAL:
OPERATING TEMPERATURE, -20 TO +70 DEGREES C, PER EIA 448, METHOD 10
STORAGE TEMPERATURE, -25 TO +85 DEGREES C
HUMIDITY AND TEMPERATURE CYCLING PER EIA-364-31B, METHOD III
TEMPERATURE LIFE PER EIA-364-17B, METHOD B, TEMPERATURE TEST CONDITION 3, TIME CONDITION B
THERMAL SHOCK, PER EIA-364-32C, -25 TO 85 DEGREES C
SOLDERABILITY, PER EIA-364-52, CLASS 2, CATEGORY 1, 95% MINIMUM COVERAGE
RESISTANCE TO SOLDER HEAT, PER 109-202, CONDITION B

△ 1 COUNTRY OF ORIGIN AND TE LOGO LOCATED APPROXIMATELY AS SHOWN

2 ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003 (ROHS)".

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN 29MAR05		 Tyco Electronics Corporation Harrisburg, PA 17105-3608		
		CHK M SARVER 29MAR05				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME SLIDE SWITCH, RIGHT ANGLE		
	0 PLC ± -		APVD M SARVER 29MAR05			
	1 PLC ± -		PRODUCT SPEC			
	2 PLC ± 0.2		—			
	3 PLC ± -		APPLICATION SPEC			
4 PLC ± -		—		SIZE		
MATERIAL		FINISH		CAGE CODE		
SEE NOTES		SEE NOTES		DRAWING NO		
		WEIGHT		RESTRICTED TO		
		—		A2 00779 C-1825232		
		CUSTOMER DRAWING		SCALE 6:1		
				SHEET 1 OF 1		
				REV B2		

1825232

B

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1825232-1](#)