






PROD		LOC	DIST	P	F	ZONE	LTR	REVISIONS		DATE	APPD
5327		DF	F0					DESCRIPTION			
CODE								REV PER 0600-6175-97		CT	DG
										9-97	



- △ CUSTOMER P/N, 00779 AND DATE CODE INK STAMPED IN THIS APPROXIMATE AREA.
- △ NUMBERS INDICATING END POSITIONS STAMPED THIS SIDE ONLY.
- 3. MEETS ALL APPLICABLE REQUIREMENTS OF MIL-C-55302.
- △ MINIMUM PAD LENGTH ON CIRCUIT BOARD.
- △ CONTACT FINISH: TABS TIN-LEAD PLATED FOR SOLDERABILITY OVER NICKEL PER MIL-C-55302.
- △ HOUSING MATERIAL: LIQUID CRYSTAL POLYMER PER MIL-M-24519, GLCP-30F; COLOR: GRAY.
- △ CONTACT MATERIAL: BRASS
- △ PIN PROTECTOR MATERIAL: VELOSTAT OR EQUIVALENT LOW STATIC OR ANTI-STATIC POLYETHYLENE. COLOR: PINK
- △ EPOXY SEALANT IS ADDED TO HOUSING WHERE CONTACTS EMERGE FROM HOUSING.





RECM. P.C. BD. LAYOUT



SECTION X-X
TYPE I

SECTION X-X
TYPE II

	I I	09344S0CNPC78667-2	3.150 [80.01]	63	3.850 [97.79]	3.600 [91.44]	3.670 [93.22]	3.450 [87.63]	128	532046-2
OBSOLETE	I	09344/PC78667-1	3.150 [80.01]	63	3.850 [97.79]	3.600 [91.44]	3.670 [93.22]	3.450 [87.63]	128	532046-1
	TYPE	CUSTOMER PART NUMBER	Z	Y	X	U	T	S	NO. OF POSN.	PART NUMBER
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES [mm] TOLERANCES ON + 2 PLC DEC ± 3 PLC DEC ±.005 [.013] ANGLES ± 0° 30'					DR 3-12-90 T.WIEST		<div> AMP INCORPORATED Harrisburg, Pa. 17105</div>			
					CHK 12-31-91 D.GUTTER					
MATERIAL CONTACT: BRASS HOUSING: 					APPD 12-31-91 D.GUTTER		NAME MINI BOX, PIN HEADER, EDGE MOUNT, CONNECTOR ASSEMBLY			
					APPD 12-31-91 D.GUTTER					
FINISH					PRODUCT SPEC -		SIZE D FSCM NO 00779 DRAWING NO 532046			
					APPLICATION SPEC -					
					WEIGHT -		SCALE 4:1 SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[532046-2](#)