

THIS IS A CONTROLLED DOCUMENT.

1281 (7/63)

APPLICATOR PARTS LIST

TYPE **LENGTHWISE BRUSH CONTACT AMPLIVAR**

MAGNET PICKUP WIRE STOP
AMP INCORPORATED HARRISBURG, PENNA.
 RIGHT HAND

NO.	DESCRIPTION	REQ.	PART NO.	NO.	DESCRIPTION	REQ.	PART NO.	CRIMPING DATA			TERMINALS	
								CMA	CRIMP	HT.		
1	WIRE CRIMPER	1	4539173	42				700	.057		62214-2	
2	INS. CRIMPER			43				800	.058			
3	ANVIL	1	14734050	44	HOLD DOWN (100 HIGH)	1	375826	1000	.060			
4	ANVIL SPACER			45				1200	.061			
5	SHEAR BLADE	1	4570862	46				1400	.063			
6	REAR SHEAR PLATE	1	3850134	47				1600	.063			
7	SHEAR BLADE SPACER	2	370954	48				1800	.064			
8	FRONT SHEAR PLATE	1	372064	49				2000	.066			
9	REAR ANVIL SPACER PLT.			50				CRIMP	SIZE	TYPE		FEED
10	FRONT ANVIL SPACER PLT.			51				WIRE	.090	F		
11	TOOL SPACER	1	370439	52				INSUL.				.500
12	CRIMP SPACER			53	HOLD DOWN (BLADE MT)	1	18112271	SLEEVED				
13	FRONT STRIP GUIDE	1	3790341	54				INSULATION RANGE	WIRE RANGE			
14	REAR STRIP GUIDE	1	371638	55						700-2000		
				56	FLOATING WIRE STOP	1	5650812	EXPLODED VIEW				
15	RAM	1	471911	57	BUSHING	REF	811258-2	A-6000		A-6000-1		
16	TOOL HOLDER			58	STOP	REF	811259-2	REMARKS: Δ INDICATES				
17	ADJ. CRIMP MOUNT			59	SPACER	REF	811260-1	PARTS USED ON				
18	ADJ. BLOCK			60	SLIDE	REF	811280-1	565081-2 ASSY. (ITEM 56)				
19	APPLICATOR MOUNT	1	570656	61	MOUNT	REF	811282-1	RIGHT HAND				
20	BASE PLATE			62								
21	BASE BLOCK			63	HOLDER-MAGNET	REF	811284-1					
22	STRIP GUIDE PLATE			64	BRACKET	REF	811285-1					
23	ANVIL HOLDER	1	370526	65								
24	AUX. ANVIL HOLDER	1	377515		MISCELLANEOUS							
25	STRIPPER			66	MAGNET	REF	811287-1					
26	STRIPPER MOUNT	REF	8113231	67	WIRE STOP	REF	4653442					
27	RETAINER PLATE	REF	372251	68								
28	STRIPPER MOUNT BRACKET			69								
29	STRIPPER BUSHING			70								
30	STOCK DRAG	1	375381	71	TENSION ADJ. PLATE	1	374999					
31	STOCK DRAG HANDLE			72								
32	STOCK DRAG STUD	2	354045-1	REV.	REVISION RECORD	DATE	BY	ECN	THIS APPLICATOR IS TO BE USED ON			
33	STOCK DRAG SPRING	2	1238471	A	ECN A-395892	9-92	MO/TE	-	AMP-O-LECTRIC 1-471273-3			
34	STOCK DRAG ADJ. SCREW	2	372997	A1	ECN 0150-0249-03	3-03	MY/TE		ALIGN. GA. 679597-1			
35	FEED FINGER HOLDER								SERIAL NO.	DATE SHIPPED	DESIGNED	
36	FEED FINGER	1	375093								R. Bennett 12-26-74	
37	FEED FINGER TIP								CUSTOMER NAME AND ADDRESS		CHK'D.	
38	FEED FINGER SPACER										1-7-75	
39	BASE CASTING	1	570238								APP'D.	
40	GUARD ASSY.	1	4576642						APPLICATOR NUMBER	REV.	SHEET	
41									A1	5661492	1 OF 1	

ALL RIGHTS RESERVED. BY AMP INCORPORATED. RELEASED FOR REPRODUCTION.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[566149-2](#)