



DIMENSIONS: mm (In.)

SPECIFICATIONS	
Insertion and extraction force:	1 Kg. Min.
Dielectric strength for 60 seconds:	AC 500V Min.
Suitable rated current:	6.3 A 250V
Insulation resistance @ 500V DC:	100M Ω Min.
Temperature rise:	50°C Max.
Voltage drop:	20mV Max.
Body material:	flame retardant thermoplastic material

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eagle Plastic Devices:](#)

[441-EPD200H](#)