

1	2.0 dB/100m	74.3	72.3	72.3	70.3	67.8	64.8	20	100 ± 15	100 ± 15	40.0	35.0
4	3.8 dB/100m	65.3	63.3	61.5	59.5	55.8	52.7	23	100 ± 15	100 ± 15	40.0	23.0
8	5.3 dB/100m	60.8	58.8	55.4	53.4	49.7	46.7	24.5	100 ± 15	100 ± 15	40.0	16.9
10	6 dB/100m	59.3	57.3	53.3	51.3	47.8	44.8	25	100 ± 15	100 ± 15	40.0	15.0
16	7.6 dB/100m	56.2	54.3	48.7	46.7	43.7	40.7	25	100 ± 15	100 ± 15	38.0	10.9
20	8.5 dB/100m	54.8	52.8	46.3	44.3	41.8	38.8	25	100 ± 15	100 ± 15	37.0	9.0
25	9.5 dB/100m	53.3	51.3	43.8	41.8	39.8	36.8	24.3	100 ± 15	100 ± 15	36.0	7.0
31.25	10.7 dB/100m	51.9	49.9	41.2	39.2	37.9	34.9	23.6	100 ± 15	100 ± 15	35.1	5.1
62.5	15.4 dB/100m	47.4	45.4	32	30	31.9	28.9	21.5	100 ± 15	100 ± 15	32.0	
100	19.8 dB/100m	44.3	42.3	24.5	22.5	27.8	24.8	20.1	100 ± 15	100 ± 15	30.0	
155	25.2 dB/100m	41.5	39.5	16.3	14.3	23.9	20.9	18.8	100 ± 20	100 ± 15	28.1	
200	29.0 dB/100m	39.8	37.8	10.8	8.8	21.8	18.8	18	100 ± 20	100 ± 15	27.0	
250	32.8 dB/100m	38.3	36.3	5.5	3.5	19.8	16.8	17.3	100 ± 20	100 ± 15	26.0	

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation	Storage
75°C	-40°C To +75°C	0°C To +60°C	-40°C To +75°C

Bend Radius

Installation Min.

4.7 in (120 mm)

Max. Pull Tension:	40 lbs (18 kg)
Bulk Cable Weight:	122 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Marine, Indoor, Outdoor, Non-Halogenated, Sunlight Resistance
Flammability / Reaction to Fire:	UL CMG-LS, FT4, IEEE 1202
NEC / UL Compliance:	Article 800
CEC / C(UL) Compliance:	CMG-ST1
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Data Category:	Category 6
TIA/EIA Compliance:	Category 6 - TIA 568.2-D
ISO/IEC Compliance:	IEC 61034-2 - Smoke Density Min Transmittance = IEC 60332-3-22
European Halogen Free Standards:	IEC 60754-1 - Halogen Amount = Jacket only
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2017-07-10
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Jacket sequentially marked at 2 ft. intervals.
--------	--

History

Update and Revision:	Revision Number: 0.230 Revision Date: 03-27-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
777940T 0105000	Black	Reel	305 m	612825189138
777940T 0101000	Black	Reel	305 m	

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[777940T 0101000](#)