

Part Number: 1506ABHDL
6 GHz RG59 BNC Connector



Product Description

RG-59, 6 GHz, HD, BNC, Plenum, 1 piece connector

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	HD-SDI, Video, Digital Video, SMPTE 2081-1 6 Gb/s UHDTV, SMPTE 424M 3 Gb/s HD-SDI 1080P

Physical Characteristics (Overall)

Conductor Size:	20 AWG
Packaging:	50 per package

Connectors

Materials

Description	Material
	Nut
Brass, Nickel Plated	
Body	Brass, Nickel Plated
Contact	Brass, Gold Plated
Insulator	PTFE

Electrical Characteristics

Return Loss (RL)

Frequency [MHz]	Minimum Return (RL)
5-1485	15 dB
1485-3000	10 dB
3000-4500	7 dB

Electrical Characteristics Notes:	SMPTE 2081-1 Return Loss or better to 4.5 GHz
-----------------------------------	---

Mechanical Characteristics

Footprint/Type:	Coax
Connector Interface Type:	BNC
Connector Series Name:	HD
Locking:	Yes
Tool Compatibility:	CPLCRBC-BR (compression), PSA59/6 (strip)
Termination Type:	Compression
Cable Center Conductor Diameter Limits:	0.0295 - 0.0322 in
Cable Dielectric Diameter Limits:	0.1259 - 0.1377 in
Cable Outer Jacket Diameter Limits:	0.1870 - 0.2007 in

Standards

RG Type:	59/U Type
----------	-----------

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	No

Part Number

Variants

Item #	Color	Footnote
1506ABHDL	Red	Q

Footnote:	Q - STANDARD PACKAGES CANNOT BE BROKEN.
-----------	---

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[1506ABHDL](#)