

CONFIDENTIAL

VERTRAULICH

THIS DRAWING IS THE EXCLUSIVE PROPERTY OF MARQUARDT. WITHOUT THEIR CONSENT IT MAY NOT BE REPRODUCED OR GIVEN TO THIRD PARTIES.

Alle Rechte bei Marquardt, auch fuer den Fall von Schutzrechtsanmeldungen. Jede Veruegungsbefugnis, wie Kopier- und Weitergaberecht, bei uns.

A	recommended cut-out for snap-in fixing (edge opposite to snap-in direction)	1	2	3	4
			wall thickness	length of cut-out	width of cut-out
			0.75 ... 1	30+0.1	22.2+0.2
			>1 ... 1.5	30.2+0.1	22.2+0.2
		>1.5 ... 3	30.4+0.1	22.2+0.2	

Marking
MARQUARDT 1660.
16(4)/250~ T85/55

DPST
Rubber seal between actuator and housing
Neon lamp with Rv for 230 V AC
Total travel 4 ±0.4
Suitable for appliances of class II
Actuating side protected acc. to DIN 40 050, IP54

"The IP-protection mentioned in our documents refers to the actuating side of the switch. The sealing between switch and customer appliance and the testing of the tightness have to be effected by the customer."

-	-	-	1660.5202-XX
Figure	Type	Customer No.	Art.No.-PI

General tolerances				Sheet 01			Ident.	Document number	Index			
All dimensions are in millimetres	Shape and location 	Angle ± 2 °	Edge tolerance 	Length	Radii	Format DIN A4	Projection 	Scale 1:1	K	16605202	k	
				0-6	± 0.2							± 0.2
				>6-15	± 0.4							±
				>15-30	± 0.4							±
				>30-70	± 0.6							±
				>70-120	±							±
>120	±	±										
k	131663	2020-09-08	PANDHAREA			System	NX V11.0	Appliance Switch				
j	36501	2003-10-27	VOR									
i	32547	2002-05-21	WJ									
h	28075	1999-10-12	MUT			Replacement of Zg.gl.Nr.v.14.09.1995	 MARQUARDT					
Index	MEC-No.	Date (YYYY-MM-DD)	Edited by									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marquardt:](#)

[01660.5202-00](#) [01660.5202-01](#)