

CONFIDENTIAL

VERTRAULICH

THIS DRAWING IS THE EXCLUSIVE PROPERTY OF MARQUARDT. WITHOUT THEIR CONSENT IT MAY NOT BE REPRODUCED OR GIVEN TO THIRD PARTIES.

Alle Rechte bei Marquardt, auch fuer den Fall von Schutzrechtsanmeldungen. Jede Veruegungsbefugnis, wie Kopier- und Weitergaberecht, bei uns.

A	recommended cut-out for snap-in fixing (edge opposite to snap-in direction)	1	2	3	4
		wall thickness	length of cut-out	width of cut-out	
		0.75 to 1	30 +0.1	22.2 +0.2	
		>1 to 1.5	30.2 +0.1	22.2 +0.2	
		>1.5 to 3	30.4 +0.1	22.2 +0.2	

DPNO
Total travel 4.5±0.4
Suitable for appliances of class II

Marking
MARQUARDT®
1661.
16(4)/250~ T85/55

Code of manufacture: place/year/week
On box: Customer Part No. see variant table

-		-		23048		1661.0101-XX			
Figure		Type		Customer Part No.		Art.No.-PI			
Shape and location	Angle ± 2 °	Length		Radii		Sheet 01	Ident. K	Document number 16610101	Index h
	Edge tolerance	0-6 ± 0.2	±	± 0.2	±				
		>6-15 ± 0.4	±	±	±	All dimensions are in millimetres	Appliance Switch		
		>15-30 ± 0.4	±	±	±				
		>30-70 ± 0.6	±	±	±	System NX V1872	MARQUARDT		
		±	±	±	±				
h	137245	2021-04-30		JOSHIO		Replacement of			
g	40663	2004-07-12		WJ					
f	32547	2002-05-23		SIG		Zg.gl.Nr.v.24.09.1998			
e	28075	1999-10-12		MUT					
Index	MEC-No.	Date (YYYY-MM-DD)		Edited by					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marquardt:](#)

[01661.0101-00](#)