

CONFIDENTIAL

VERTRAULICH

Alle Rechte bei Marquardt, auch fuer den Fall von Schutzrechtsanmeldungen. Jede Veruegungsbefugnis, wie Kopier- und Weitergaberecht, bei uns.

THIS DRAWING IS THE EXCLUSIVE PROPERTY OF MARQUARDT. WITHOUT THEIR CONSENT IT MAY NOT BE REPRODUCED OR GIVEN TO THIRD PARTIES.

	1	2	3	4	
A	recommended cut-out for snap-in fixing (edge opposite to snap-in direction)		wall thickness	length of cut-out	width of cut-out
			0.75 to 1.25	19.2 -0.1	12.9+0.1
			1.25 to 2	19.4 -0.1	12.9+0.1
		2 to 3	19.8 -0.1	12.9+0.1	

  
  
  

Marking

Ⓜ

168..

16 (4) / 250 ~

12 (8) / 250 ~

10 (8) / 250 ~ 5E4

T100/55

12A 125-250 VAC

1/2 HP 125-250 VAC

R97

1 — 1a

2 —

Code of manufacture:  
place/year/week

operating position	h
OFF	23.9
ON	20.85
block	19.7

  

SPST

Suitable for appliances of class II

-	-	-	1683.1101-XX
Figure	Type	Customer Part No.	Art.No.-PI
Shape and location	Angle ± 2 °	Sheet 01	
	Edge tolerance	Ident. K	Document number 16831101
Ⓜ		Format DIN A4	Index c
		Projection	Scale 1:1
All dimensions are in millimetres		Appliance Switch	
c	137026	2021-08-17	MATHPATIR
b	41382	2004-10-25	HHE
a	31290	2001-02-20	GRH
	31167	2001-01-25	GRH
Index	MEC-No.	Date (YYYY-MM-DD)	Edited by
		System NX V1872	Replacement of
		Zg.gl.Nr.v.25.01.2001	
		<b>MARQUARDT</b>	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marquardt:](#)

[01683.1101-03](#)