

CONFIDENTIAL

VERTRAULICH

Alle Rechte bei Marquardt, auch fuer den Fall von Schutzrechtsanmeldungen. Jede Veruegungsbefugnis, wie Kopier- und Weitergaberecht, bei uns.

THIS DRAWING IS THE EXCLUSIVE PROPERTY OF MARQUARDT. WITHOUT THEIR CONSENT IT MAY NOT BE REPRODUCED OR GIVEN TO THIRD PARTIES.

	1	2	3	4	
A	recommended cut-out for snap-in fixing (edge opposite to snap-in direction)		wall thickness	length of cut-out	width of cut-out
			0.75 to 1.25	19.2 -0.1	12.9+0.1
			1.25 to 2	19.4 -0.1	12.9+0.1
		2 to 3	19.8 -0.1	12.9+0.1	

Marking

Ⓜ

168..

16 (4) / 250 ~

12 (8) / 250 ~

10 (8) / 250 ~ 5E4

T100/55

12A 125-250 VAC

1/2 HP 125-250 VAC

R97

1 — 1a

2 —

Code of manufacture:
place/year/week

operating position	h
OFF	23.9
ON	20.85
block	19.7

DPST

Suitable for appliances of class II

-	-	-	1684.1101-XX																																			
Figure	Type	Customer Part No.	Art.No.-PI																																			
Shape and location	Angle ± 2 °	Sheet 01																																				
	Edge tolerance	Ident. K	Document number 16841101																																			
Ⓜ	<table border="1" style="width:100%; border-collapse: collapse;"> <tr> <th colspan="2">Length</th> <th colspan="2">Radii</th> </tr> <tr> <td>0-6</td> <td>± 0.15</td> <td>0-6</td> <td>± 0.2</td> </tr> <tr> <td>>6-15</td> <td>± 0.2</td> <td>>6-15</td> <td>± 0.3</td> </tr> <tr> <td>>15-30</td> <td>± 0.25</td> <td>>15-30</td> <td>± 0.5</td> </tr> <tr> <td>>30-70</td> <td>± 0.4</td> <td>>30-70</td> <td>± 10%</td> </tr> <tr> <td>>70-120</td> <td>± 0.6</td> <td>>70-120</td> <td>± 10%</td> </tr> <tr> <td>>120-200</td> <td>± 1</td> <td>>120-200</td> <td>± 10%</td> </tr> <tr> <td></td> <td>±</td> <td></td> <td>±</td> </tr> <tr> <td></td> <td>±</td> <td></td> <td>±</td> </tr> </table>	Length		Radii		0-6	± 0.15	0-6	± 0.2	>6-15	± 0.2	>6-15	± 0.3	>15-30	± 0.25	>15-30	± 0.5	>30-70	± 0.4	>30-70	± 10%	>70-120	± 0.6	>70-120	± 10%	>120-200	± 1	>120-200	± 10%		±		±		±		±	Index c
		Length		Radii																																		
0-6	± 0.15	0-6	± 0.2																																			
>6-15	± 0.2	>6-15	± 0.3																																			
>15-30	± 0.25	>15-30	± 0.5																																			
>30-70	± 0.4	>30-70	± 10%																																			
>70-120	± 0.6	>70-120	± 10%																																			
>120-200	± 1	>120-200	± 10%																																			
	±		±																																			
	±		±																																			
c	137026	2021-07-19	JOSHIO																																			
b	41382	2004-10-25	HHE																																			
a	31290	2001-02-20	GRH																																			
	28464	2001-01-25	GRH																																			
Index	MEC-No.	Date (YYYY-MM-DD)	Edited by																																			
		All dimensions are in millimetres																																				
		Format DIN A4	Projection Scale 1:1																																			
		System NX V1872	Replacement of Zg.gl.Nr.v.25.01.2001																																			
		Appliance Switch																																				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marquardt:](#)

[01684.1101-02](#)