




CONFIDENTIAL

VERTRAULICH

THIS DRAWING IS THE EXCLUSIVE PROPERTY OF MARQUARDT. WITHOUT THEIR CONSENT IT MAY NOT BE REPRODUCED OR GIVEN TO THIRD PARTIES.

Alle Rechte bei Marquardt, auch fuer den Fall von Schutzrechtsanmeldungen. Jede Veruegungsbefugnis, wie Kopier- und Weitergaberecht, bei uns.

	1	2	3	4	
A	recommended cut-out for snap-in fixing (edge opposite to snap-in direction)		wall thickness	length of cut-out	width of cut-out
			0.75 to 1.25	19.2 -0.1	12.9+0.1
			1.25 to 2	19.4 -0.1	12.9+0.1
			2 to 3	19.8 -0.1	12.9+0.1
B					
C					
D	Marking Ⓜ 18.. 6(4)/250~5E4 T100/55 10(4)/250~ 5/50A 250V~ 		SPST Suitable for appliances of class II		
E	6A 125-250V AC 1/4 HP 125V AC 1/2 HP 250V AC R 30				
Code of manufacture: place/year/week					
On Box: Customer Part No. see variant table					

-		-				132 576-00		1801.1102-XX				
Figure		Type				Customer Part No.		Art.No.-PI				
<div>Shape and location</div> <div></div>		Angle ± 2 °		Length		Radii		Sheet 01		Ident. K	Document number 18011102	Index h
				0-6 ± 0.2		± 0.2		Format DIN A4	Projection 			
		Edge tolerance		± 0.4		±						
		± 0.4		±		±						
		±		±		±						
		±		±		±						
		±		±		±						
		±		±		±						
		±		±		±						
		±		±		±						
h		137838		2021-05-28		JOSHIO		All dimensions are in millimetres		Appliance Switch		
g		43724		2005-07-19		vor						
f		25489		1997-10-28		GRH						
e		25088		1997-06-24		SIG						
Index		MEC-No.		Date (YYYY-MM-DD)		Edited by		Replacement of Zg.gl.Nr.v.24.06.1997		 MARQUARDT		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marquardt:](#)

[01801.1102-02](#)