












A	1	2	3	4
	recommended cut-out for snap-in fixing (edge opposite to snap-in direction)	wall thickness	length of cut-out	width of cut-out
		0.75 to 1.25	19.2-0.1	12.9+0.1
		1.25 to 2	19.4-0.1	12.9+0.1
B		2 to 3	19.8-0.1	12.9+0.1
C	 			
				
D	<p>Marking</p> <p>1803. 6(4)/250~5E4 10(4)250~ T100/55</p> 			
	<p>SPDT Suitable for appliances of class II</p> 			
E	<p>6A 125-250V AC 1/4HP 125V AC 1/2HP 250V AC R30  </p> <p>Code of manufacture: place/year/week</p>			
				

-		-				-		1803.1102-XX					
Figure		Type				Customer Part No.		Art.No.-PI					
<div>Shape and location</div> <div></div>		Angle $\pm 2^\circ$		Length		Radii		Sheet 01		Ident. K	Document number 18031102	Index h	
				Edge tolerance									Format DIN
				0-6	$\pm 0.2$		$\pm$	0-6	$\pm 0.2$		1:1	Appliance Switch	
		>6-15		$\pm 0.4$		$\pm$		$\pm$					
		>15-30		$\pm 0.4$		$\pm$		$\pm$					
				$\pm$		$\pm$		$\pm$					
				$\pm$		$\pm$		$\pm$					
				$\pm$		$\pm$		$\pm$					
				$\pm$		$\pm$		$\pm$					
				$\pm$		$\pm$		$\pm$					
h	137892	2021-07-29		PANDHAREA		All dimensions are in millimetres		System NX V1872		 MARQUARDT			
g	66315	2009-11-30		MUT									
f	64510	2009-10-01		MUT									
e	29280	2000-05-17		SIG									
Index	MEC-No.	Date (YYYY-MM-DD)		Edited by		Replacement of Zg.gl.Nr.v.17.05.2000							

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marquardt:](#)

[01803.1102-00](#)