




A	1	2	3	4
	recommended cut-out for snap-in fixing (edge opposite to snap-in direction)	wall thickness	length of cut-out	width of cut-out
		0.75 to 1.25	19.2-0.1	12.9+0.1
		1.25 to 2	19.4-0.1	12.9+0.1
B				SPDT With centre-off Suitable for appliances of class II G=matching IEC 60335-1:2001 clause 30
C				
D	Marking Ⓜ 1808. μ 6(2)/250~T100/55 	6A 125-250V AC 1/8HP R58		
E	Code of manufacture: place/year/week On box: Customer Part No. see variant table G			

-		-				9000152634			1808.1112-XX				
Figure		Type				Customer Part No.			Art.No.-PI				
<div>Shape and location</div> <div></div>		<div>Angle ± 2 °</div> <div>Edge tolerance</div> <div></div>		Length		Radii		Sheet 01			Ident. K	Document number 18081112	Index g
				0-6	± 0.2		±	0-6	± 0.2	Format DIN A4			
				>6-15	± 0.4		±		±				
				>15-30	± 0.4		±		±				
					±		±		±				
					±		±		±				
					±		±		±				
					±		±		±				
					±		±		±				
					±		±		±				
g	137894	2021-06-09		JOSHIO		All dimensions are in millimetres			Appliance Switch				
f	98181	2015-10-28		MUT									
e	64492	2009-10-20		MUT		System NX V1872			 MARQUARDT				
d	47137	2006-04-12		vor									
Index	MEC-No.	Date (YYYY-MM-DD)		Edited by		Replacement of Zg.gl.Nr.v.28.11.1996							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marquardt:](#)

[01808.1112-01](#)