

Aufschrift:

Marking:

2420.4101

14(4) / 250 ~ μ 50E3

10

Herstelldatum:

Herstellort/ -jahr/ -woche/ -tag
nach Marquardt Standard

Date code of manufacture:

plant / year / week / day
acc. to Marquardt standard

Kraft in Ruhestellung

force in free position

24 N ± 10 N

Kraft an Schaltpunkt

force at operating position

30 N ± 10 N





Kraft in Endstellung

force at total travel position

35 N ± 10 N

Beigelegte Bedienungsanleitung beachten

Please observe user manual for further information

-	-	-	2420.4101-XX			
Figure	Type		Customer No.		Art.No.-Pl	
General tolerances			Sheet 01		Ident. K	
All dimensions are in millimetres	Shape and location 	Angle $\pm 2^\circ$ 	Edge tolerance 	Length	Radii	
				0-6	± 0.15	± 0.2
				>6-15	± 0.2	± 0.3
				>15-30	± 0.25	± 0.5
				>30-70	± 0.4	
				>70-120	± 0.6	$\pm 10\%$
				>120	± 0.8	
c	117290	2018-07-17	TRIGUIK		System NX V11.0	
b	74959	2011-08-25	FRT			
a	73342	2011-04-19	HHE			
	70523	2011-01-26	FRT			
Index	MEC-No.	Date (YYYY-MM-DD)	Edited by		Replacement of V09111501	
					foot switch	
					 MARQUARDT	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marquardt:](#)

[02420.4101-01](#)