

9037.0100

Product number

Actuation type	direct	
Weight	8.300 g	
Diameter	6.5	
Switching function	Step switch	
Material fixed contact	CuSn gold-plated	
Number of poles	1 - pole	
Connections	PCB terminal	
Mechanical life endurance	3E4	
Contact system	1E4	
Rating IEC	0.4 A 28 V	
Contact resistance (new condition)	< 50 mOhm	
Insulation resistance (new condition)	> 100 MOhm	
Voltage strength at 250 V	Function insulation / Basic insulation	null V
	Reinforced insulation	null V
	Small contact distance	> 500 V

Actuators	rotary axis, CurZn nickel-plated	
Housing description	threaded socket: CnZn nickel-plated housing: zinc, rubber seal base plate: black, PA glass fiber-reinforced	
Connection surface	Bearing connection External connection	gold plated gold plated
Contact material	CuSn gold-plated	
Contact type	slide contact	
Miscellaneous	with 12 switching positions corresponding rotary knob of black thermoplastic switching angle 30°/ step	
Type of fastening	central fastening M6 x 0.75	

All information subject to possible technical changes

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marquardt:](#)

[09037.0100-00](#)