

# 9037.0400

## Product number

|                                       |  |         |
|---------------------------------------|--|---------|
| Actuation type                        | direct                                 |         |
| Weight                                | 8.300 g                                |         |
| Diameter                              | 6.5                                    |         |
| Switching function                    | Step switch                            |         |
| Material fixed contact                | CuSn gold-plated                       |         |
| Number of poles                       | 4 - pole                               |         |
| Connections                           | PCB terminal                           |         |
| Mechanical life endurance             | 3E4                                    |         |
| Contact system                        | 1E4                                    |         |
| Rating IEC                            | 0.4 A 28 V                             |         |
| Contact resistance (new condition)    | < 50 mOhm                              |         |
| Insulation resistance (new condition) | > 100 MOhm                             |         |
| Voltage strength at 250 V             | Function insulation / Basic insulation | null V  |
|                                       | Reinforced insulation                  | null V  |
|                                       | Small contact distance                 | > 500 V |

|                            |   |             |
|----------------------------|---|-------------|
| <b>Actuators</b>           | rotary axis, CurZn nickel-plated  |             |
| <b>Housing description</b> | threaded socket: CnZn nickel-plated<br>housing: zinc, rubber seal<br>base plate: black, PA glass fiber-reinforced |             |
| <b>Connection surface</b>  | Bearing connection  | gold plated |
|                            | External connection   | gold plated |
| <b>Contact material</b>    | CuSn gold-plated  |             |
| <b>Contact type</b>        | slide contact   |             |
| <b>Miscellaneous</b>       | with 3 switching positions corresponding<br>rotary knob of black thermoplastic<br>switching angle 30°/ step       |             |
| <b>Type of fastening</b>   | central fastening M6 x 0.75   |             |

All information subject to possible technical changes

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marquardt:](#)

[09037.0400-00](#)