

# 9040.2101

Product number

Actuation type	direct	
Weight	5.600 g	
Switching function	Changeover switch (TPDT)	
Number of poles	1 - pole	
Connections	Solder terminal, sealed	
Mechanical life endurance	1E5	
Contact system	5E4	
Rating IEC	4 A 30 V DC 5 A 48 V AC	
Contact resistance (new condition)	< 20 mOhm	
Insulation resistance (new condition)	> 1000 MOhm	
Voltage strength at 250 V	Function insulation / Basic insulation	null V
	Reinforced insulation	null V
	Small contact distance	> 1000 V
Actuators	lever, CuZn chrome-plated, flat lever	
Housing description	base plate: olivegreen bracket plate: stainless steel threaded socket: CuZn nickel-plated	
Connection surface	Bearing connection	silver plated
	External connection	silver plated
Contact material	Ag	

**Contact type**

lifting contact

---

**Miscellaneous**

locking ring and toothed washer of  
galvanised and chromated steel

---

**Type of fastening**

central fastening M6 x 0.75

All information subject to possible technical changes

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marquardt:](#)

[09040.2101-00](#)