

9041.0101

Product number

Actuation type	direct	
Weight	5.200 g	
Switching function	Changeover switch with OFF position in the center (SPDT - Center OFF)	
Number of poles	1 - pole	
Connections	Solder terminal, sealed	
Mechanical life endurance	1E5	
Contact system	5E4	
Rating IEC	5 A 48 V AC 4 A 30 V DC	
Contact resistance (new condition)	< 20 mOhm	
Insulation resistance (new condition)	> 1000 MOhm	
Voltage strength at 250 V	Function insulation / Basic insulation	null V
	Reinforced insulation	null V
	Small contact distance	> 1000 V
Actuators	lever, CuZn chrome-plated	
Housing description	threaded socket: CnZn nickel-plated, hexagonal nuts of nickel-plated CuZn base plate: olivegreen bracket plate: stainless steel	
Connection surface	Bearing connection	silver plated
	External connection	silver plated

Contact material

Ag

Contact type

lifting contact

Miscellaneous

locking ring and toothed washer of galvanised and chromated steel

Type of fastening

central fastening M6 x 0.75

All information subject to possible technical changes

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marquardt:](#)

[09041.0101-00](#)