



zul. Endstellung
total travelled
position allowed

Schaltpunkt
operating position

Ruhestellung
free position

Empfohlenes Lochbild
Toleranzen nach DIN IEC 326
Teil 3 sehr fein
(Leiterplattendicke 1.5)

recommended hole pattern,
tolerances according
to DIN IEC 326 item 3 very fine
(pc plate thickness 1.5)



Aufschrift
Marking

Ⓜ
1050 μ

5/250~ 10

50E3 T100

5A 125-250V AC 1/10HP
R 56

Herstelljahr/-woche
nach DIN EN 60062

Wechsler 1-polig
single pole changeover

Schalt-Betätigungskraft
actuating force ≤ 0.50 N

Rückschaltkraft
release force ≥ 0.10 N

Differenzweg
movement differential ≤ 1.0 mm

Gehäuse auf Anschlußseite abgedichtet
housing sealed on terminal side

Schutzvermerk
nach DIN 34 beachten
COPYRIGHT RESERVED

Allgemeintoleranzen/UNTOLERANCED DIMENSIONS				PROJECTION		Pause COPY	Blatt von SHEET OF		Zeichn./DRAWING NO.		
Für Längen und Radien FOR LENGTHS AND RADII.	Abmaße in mm Für Nennmaßbereich in mm ALL DIMENSIONS ARE IN MILLIMETRES						Original DIN A4	Maßstab SCALE 2:1	5	1050.7202	
	±	bis/UP TO 6	über/OVER 6 bis/UP TO 30			über/OVER 30					
	0.2	0.3				0 10 20 30 mm		Schnappschalter Snap Action Switch			
d				i		gez./DRAWN BY 26.03.93 Ble					 Marquardt GmbH, D-78604 Riethim-Weilheim
c				h		Ersatz für/REPLACEMENT OF					
b	29551	21.06.00	pfu	g							
a	0	18.09.96	gue	f							
				e							
Ausg. ISSUE	Änderung REVISION	gez. DRAWN BY		Ausg. ISSUE	Änderung REVISION	gez. DRAWN BY					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marquardt:](#)

[1050.7202](#)