


Full or partial part number

Home / LED Indication / Flexible Light Pipes / FLP System

Flexible Light Pipes, LED Indication

FLP System



Available Options:

Adapter LED Color/Wavelength

Adapter Optical Fiber Diameter

Lens Size

Lens Profile

Panel Cutout

Luminous Intensity

Optical Fiber Length

Optical Fiber Color

[clear](#)



Part Number:

FR4-5.0-SUR-F5P-6

Categories: [FLEXIBLE LIGHT PIPES](#)

[LED INDICATION](#)

[Request Sample](#)

[Check Stock](#)

[Download Data Sheet](#)

[Download 3D Drawing](#)

[Download RoHS Docs](#)

[View List](#) →

### Additional information

<b>Adapter LED Color/Wavelength</b>	Amber/605nm, Amber/620nm, Blue/466nm, Blue/470nm, Green/563nm, Green/568nm, Green/570nm, Green/568nm, N/A, Orange/620nm, Red 625nm / Green 568nm, Red 625nm/Green 568nm, Red 645nm / Green 568nm, Red/625nm, Red/640nm, Red/640nmnm, Red/645nm, Red/660nm, Turquoise/500nm, White/6000K, White/6500K, Yellow 585nm / Green 565nm, Yellow 585nm/Green 565nm, Yellow 590nm / Green 568nm, Yellow 590nm/Green 515nm, Yellow 590nm/Green 568nm, Yellow 590nm/Green568nm, Yellow/585nm, Yellow/588nm, Yellow/590nm
<b>Adapter Optical Fiber Diameter</b>	1mm, 2mm
<b>Lens Size</b>	3.2 x 6.4 mm, 3.2mm x 6.4mm, 4.0mm, 4.2mm, 5.1mm, 6.0mm IP67, 6.7mm x 4.2mm, 7.0mm, 9.0mm IP67, N/A
<b>Lens Profile</b>	Dome, Flat, Low Profile, Low Profile Diffused, Low Profile Fresnel, N/A
<b>Panel Cutout</b>	N/A, Oval, Rectangular, Round
<b>Luminous Intensity</b>	100mcd/60mcd, 120mcd, 15/5 mcd, 1500mcd, 15mcd/5mcd, 200mcd, 2200mcd, 250mcd, 300mcd, 350mcd, 400/80 mcd, 400mcd, 50mcd, 50mcd/50mcd, 6000mcd, 600mcd, 60mcd, 65mcd, 6mcd/8mcd, 70mcd, 800mcd, 8mcd/8mcd, 900mcd, N/A
<b>Optical Fiber Length</b>	1.0 in., 1.5 in., 10.0 in., 100.0 in., 118.0 in., 12.0 in., 12.3 in., 13.0 in., 14.0 in., 15.0 in., 18.0 in., 2.0 in., 2.1 in., 2.3 in., 2.5 iin., 2.5 in., 2.9 in., 24.0 in., 3.0 in., 3.25 in., 3.28 in., 3.5 in., 3.9 in., 36.0 in., 4.0 in., 4.1 in., 4.5 in., 5.0 in., 6.0 in., 6.5 in., 6.7 in., 8.0 in., 9.0 in., 9.5 in., N/A
<b>Optical Fiber Color</b>	Black, Blue, Green, N/A, Red, White, Yellow



Keep up with Bivar

Email\*

[Subscribe](#)

- Products
- LED Indication
- Positioning Components
- Securing Circuit Cards
- Linear LED Lighting
- Smart Technology

- Solutions
- Engineered Solutions
- Industries
- Security & Surveillance
- Communication
- Industry 4.0

- Company
- Contact Us
- About Us
- How to Buy

### BIVAR CORPORATE OFFICE

4 Thomas  
Irvine, CA 92618

TEL: 800-767-3652  
FAX: 949-951-3974

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[FR4-5.0-SUR-F5P-6](#)