

FLEXIBLE LP ASSY Part No.	LED Part No.	Peak Wavelength	Emitted Color	Optical Data @ 20mA		
		λ_p (nm)		Vf (V)		LED Iv (mcd)
				TYP	MAX	TYP
SINGLE COLOR LED ASSEMBLIES (20mA)						
FV2-X.X-UB-F6PX67PR	3UBWC-0.6K-F	470	BLUE	4.0	4.5	400
FV2-X.X-UG-F6PX67PR	3UGC-F	570	GREEN	2.1	2.4	200
FV2-X.X-UY-F6PX67PR	3UYC-F	590	YELLOW	2.0	2.4	300
FV2-X.X-UR-F6PX67PR	3URC-F	645	RED	1.7	2.4	200
BI-COLOR LED ASSEMBLIES (20mA)						
FV2-X.X-SRG-F6PX67PR	3SBCC-F	645	RED	1.7	2.4	100
		568	GREEN	2.1	2.8	60

VISIT WWW.BIVAR.COM FOR CURRENT LED DATASHEETS
LED DETAILS ON DATASHEETS TAKE PRECEDENCE OVER DETAILS SHOWN HERE

ABSOLUTE MAXIMUM RATINGS (Ta=25°C)

REVERSE VOLTAGE _____ 5V
REVERSE CURRENT _____ 100µA
OPERATING TEMPERATURE RANGE _____ -25°C ~ +85°C
STORAGE TEMPERATURE _____ -30°C ~ +100°C
LEAD SOLDERING TEMPERATURE(1/16" FROM BODY) _____ 260°C FOR 5 SECONDS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[FV2-6.0-SRG-F6PD67PR-2](#) [FV2-6.0-SRG-F6PD67PR-4](#) [FV2-6.0-SRG-F6PD67PR-5](#) [FV2-6.0-SRG-F6PD67PR-6](#)
[FV2-6.0-SRG-F6PD67PR-9](#) [FV2-6.0-SRG-F6PZ67PR-2](#) [FV2-6.0-SRG-F6PZ67PR-4](#) [FV2-6.0-SRG-F6PZ67PR-5](#) [FV2-](#)
[6.0-SRG-F6PZ67PR-6](#) [FV2-6.0-SRG-F6PZ67PR-9](#) [FV2-6.0-UB-F6PD67PR-2](#) [FV2-6.0-UB-F6PD67PR-4](#) [FV2-6.0-UB-](#)
[F6PD67PR-5](#) [FV2-6.0-UB-F6PD67PR-6](#) [FV2-6.0-UB-F6PD67PR-9](#) [FV2-6.0-UB-F6PZ67PR-2](#) [FV2-6.0-UB-](#)
[F6PZ67PR-4](#) [FV2-6.0-UB-F6PZ67PR-5](#) [FV2-6.0-UB-F6PZ67PR-6](#) [FV2-6.0-UB-F6PZ67PR-9](#) [FV2-6.0-UG-F6PD67PR-](#)
[2](#) [FV2-6.0-UG-F6PD67PR-4](#) [FV2-6.0-UG-F6PD67PR-5](#) [FV2-6.0-UG-F6PD67PR-6](#) [FV2-6.0-UG-F6PD67PR-9](#) [FV2-](#)
[6.0-UG-F6PZ67PR-2](#) [FV2-6.0-UG-F6PZ67PR-4](#) [FV2-6.0-UG-F6PZ67PR-5](#) [FV2-6.0-UG-F6PZ67PR-6](#) [FV2-6.0-UG-](#)
[F6PZ67PR-9](#) [FV2-6.0-UR-F6PD67PR-2](#) [FV2-6.0-UR-F6PD67PR-4](#) [FV2-6.0-UR-F6PD67PR-5](#) [FV2-6.0-UR-](#)
[F6PD67PR-6](#) [FV2-6.0-UR-F6PD67PR-9](#) [FV2-6.0-UR-F6PZ67PR-2](#) [FV2-6.0-UR-F6PZ67PR-4](#) [FV2-6.0-UR-](#)
[F6PZ67PR-5](#) [FV2-6.0-UR-F6PZ67PR-6](#) [FV2-6.0-UR-F6PZ67PR-9](#) [FV2-6.0-UY-F6PD67PR-2](#) [FV2-6.0-UY-](#)
[F6PD67PR-4](#) [FV2-6.0-UY-F6PD67PR-5](#) [FV2-6.0-UY-F6PD67PR-6](#) [FV2-6.0-UY-F6PD67PR-9](#) [FV2-6.0-UY-](#)
[F6PZ67PR-2](#) [FV2-6.0-UY-F6PZ67PR-4](#) [FV2-6.0-UY-F6PZ67PR-5](#) [FV2-6.0-UY-F6PZ67PR-6](#) [FV2-6.0-UY-F6PZ67PR-](#)