







(1.00 mm) .0394" PITCH • DISCRETE WIRE TERMINAL STRIP

| SERIES | NO. OF POSITIONS | PLATING OPTION | ROW OPTION | LATCH | OPTIONS | "X"R |
|--------|---|---|--|--|---|---|
| T1M | -02, -03, -05, -07, -10, -15, -20 | -F = 3 μ" (0.07 μm) Gold on contact, Matte Tin on tail | -SH = Single Row Horizontal -SV = Single Row Vertical | (Required in callout) -L = Positive Latch | -K = (4.00 mm) .157" DIA Polyimide Film Pick & Place Pad (-SH only) -P = Pick & Place Pad (-SV only) | (Leave blank for Tape & Reel) -FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) |


T1M-SH/SV
Cable Mates:
S1SS(T), S1SD(T)



-SH






-SV





View complete specifications at: samtec.com?T1M

| SERIES | NO. OF POSITIONS | PLATING OPTION | ROW OPTION | OPTION | "X"R |
|--------|--|--|--|---|---|
| T1M | -02, -03, -04, -05, -10, -15, -20 (Per Row) | -GF = 3 μ" (0.07 μm) Gold contact and tail | -DH = Double Row Horizontal -DV = Double Row Vertical | -K = (4.00 mm) .157" DIA Polyimide Film Pick & Place Pad (-DV only) | (Leave blank for Tape & Reel) -FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) |

T1M-DH/DV
Cable Mates:
S1SS(T), S1SD(T)



-DH



-DV

Note:
Some lengths, styles and
options are non-standard,
non-returnable.

View complete specifications at: samtec.com?T1M

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[T1M-14-F-SH-L](#)