





TIGER EYE™
IDC



TCSD-08-D-02.00-01-N-R

TCSD SERIES

(2.00 mm) .0787"

TIGER EYE™ IDC SOCKET CABLE

Mates with:

TMM, TMMH, STMM, MMT, TW, MTMM, EHT, ETMM (-SR), ZSTMM

SPECIFICATIONS

For complete specifications see www.samtec.com?TCSD

Insulator Material: Black Glass Filled Polyester

Contact: BeCu

Plating: Au or Sn over 50 μ" (1.27 μm) Ni

Wire: 28 AWG 7/36 Stranded, Tinned, Copper with Gray PVC Insulator

Current Rating (TCSD/STMM): 2.8 A per pin (2 pins powered)

Operating Temp Range: -40 °C to +105 °C

Lead Size Accepted: (0.48 mm) .019" to (0.53 mm) .021"

Insertion Depth: (2.87 mm) .113" to (3.17 mm) .125"

RoHS Compliant: Yes

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



ALSO AVAILABLE (MOQ Required)








- Other sizes
- Other platings

POLARIZING KEY

Specify PK-01-07 for polarizing key (Available in wheels of six each).

Also polarizes SMM Series socket strips.

Note: TCSD Series assemblies are non-standard, non-returnable.



Due to technical progress, all designs, specifications and components are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[TCSD-20-D-02.00-01-F-N](#)