


PART NAME	NEMA 4X DIE CAST ALUMINUM ENCLOSURE	PART No.	AN-1305, AN-1305-G, AN-2805 & AN-2805-B	REV. DATE	12-17-08
-----------	-------------------------------------	----------	---	-----------	----------

MATERIAL: ALUMINUM ALLOY #ADC-12

FINISH: NATURAL (NO SUFFIX)
GRAY (SUFFIX -G)
SMOOTH BLACK (SUFFIX -B)


NOTES:

- 1) FOUR (4) M4 x 20mm (0.787") LG. SCREWS SUPPLIED FOR ASSEMBLY OF COVER TO BODY.
- 2) ALL HOLE DIAMETERS HAVE ± 0.005 TOLERANCE
ALL OTHER DIMENSIONS HAVE ± 0.015 TOLERANCE




SECTION "C-C"


* DIMENSIONS ARE AT BOTTOM OF ENCLOSURE




SECTION "B-B"




DETAIL "E"





BODY



SECTION "A-A"



COVER



PART NO. AN-2805 & AN-2805-B
ARE SUPPLIED WITH A WELDED
ON MOUNTING BRACKET ONLY.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bud Industries:](#)

[AN-1305-G](#) [AN-1305](#) [AN-2805](#) [AN-2805-B](#)