

PART
NAME


ECONOCAB

PART
No.

EC-9902 TO EC-9906




TOP VIEW



SIDE VIEW

FRONT & REAR VIEW

SECTION 'A-A'

RUBBER FOOT
0.625 DIA. x 0.218 HIGH

BOTTOM VIEW

NOTES:

MATERIAL: BODY ASSEMBLY _____ 18 GA. STEEL
HANDLE _____ ABS PLASTIC
FOOT _____ RUBBER
FINISH: BODY ASSEMBLY _____ SAND TEXTURE
BLACK TEXTURE
HANDLE _____ BLACK
FOOT _____ BLACK

MOUNTING RAILS ARE PIERCED 0.281 DIA. HOLES
ON E.I.A. UNIVERSAL SPACING.

LOAD RATING: 500 LBS. MAX.

PART NO.	DIM. A	DIM. B
EC-9902	9.062	7.062
EC-9903	10.812	8.812
EC-9904	12.562	10.562
EC-9905	14.312	12.312
EC-9906	16.062	14.062

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bud Industries:

[EC-9902-BT](#) [EC-9902-S](#) [EC-9906-S](#) [EC-9903-BT](#) [EC-9903-S](#) [EC-9904-S](#) [EC-9906-BT](#) [EC-9905-S](#) [EC-9905-BT](#)
[EC-9904-BT](#)