


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO J.S.T. AND SHALL NOT BE USED OR SHOWN WITHOUT WRITTEN PERMISSION.

4			3		2		1		
ITEM	CONNECTOR PART NO.	DESCRIPTION	IPI CHECK	EOR CHECK	Applicable Tooling				
1	See Table 1	SUR CONNECTOR			BCD				
2	UL11136, 32 AWG	WHITE			TABLE 1				
					ITEM	NUMBER OF CIRCUITS	CONNECTOR PART NO.	ASSEMBLY PART NUMBER	TOTAL WIRE REQUIRED

ITEM	NUMBER OF CIRCUITS	CONNECTOR PART NO.	ASSEMBLY PART NUMBER	TOTAL WIRE REQUIRED
1	2	02SUR-32S	A02SUR02SUR32W51A	101.6 mm
1	3	03SUR-32S	A03SUR03SUR32W51A	152.4 mm
1	4	04SUR-32S	A04SUR04SUR32W51A	203.2 mm
1	5	05SUR-32S	A05SUR05SUR32W51A	254 mm
1	6	06SUR-32S	A06SUR06SUR32W51A	304.8 mm
1	8	08SUR-32S	A08SUR08SUR32W51A	406.4 mm
1	10	10SUR-32S	A10SUR10SUR32W51A	508 mm
1	12	12SUR-32S	A12SUR12SUR32W51A	609.6 mm
1	14	14SUR-32S	A14SUR14SUR32W51A	711.2 mm
1	15	15SUR-32S	A15SUR15SUR32W51A	762 mm
1	16	16SUR-32S	A16SUR16SUR32W51A	812.8 mm
1	17	17SUR-32S	A17SUR17SUR32W51A	863.6 mm
1	20	20SUR-32S	A20SUR20SUR32W51A	1,016 mm
1	22	22SUR-32S	A22SUR22SUR32W51A	1,117.6 mm



Electrical Specifications

Current: 0.5A AC/DC

Voltage: 30V DC

JST

4	Revised length tolerance	5/4/2021	SP
3	Add electrical specifications	6/27/2018	SP
2	ADDED 20 CIRCUIT ASSEMBLY	6/23/2016	SP
1	ADDED 10 CIRCUIT ASSEMBLY	6/16/2016	SP
REV.	DESCRIPTION	DATE	BY

SCALE
1:1
DIMENSIONS
All dimensions are in MM with a tolerance of +/- 5.0 unless otherwise specified.
DRAWN BY
STEVEN PILKINGTON
CHECKED BY
JUSTIN BAKER

CUSTOMER NAME	CUSTOMER PART NO.
DESCRIPTION	0.8 mm Pitch SUR Standard Catalog Assembly - 2" Inside Length - Pin out: 1 to 1
ASSEMBLY PART NO.	SEE TABLE 1
DRAWING NO. & REVISION	REVISED
GAM-004	2/25/2016

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JST:](#)

[A12SUR12SUR32W254A](#) [A04SUR04SUR32W51A](#) [A06SUR06SUR32W51A](#) [A03SUR03SUR32W51A](#)
[A14SUR14SUR32W203B](#) [A20SUR20SUR32W254A](#) [A08SUR08SUR32W51A](#) [A05SUR05SUR32W51A](#)
[A10SUR10SUR32W51A](#) [A02SUR02SUR32W51A](#)