

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO J.S.T. AND SHALL NOT BE USED OR SHOWN WITHOUT WRITTEN PERMISSION.

4		3		2		1	
ITEM	CONNECTOR PART NO.	DESCRIPTION	IPI CHECK	EOR CHECK	Applicable Tooling		
1	SACH-003G-P0.2	ACH CONNECTOR CONTACT			APPLICATOR		
2	UL1571 (spec OD), 28 AWG	WHITE					

Applicable Housings

NO. OF CIRCUITS	HOUSING PART NO.
1	ACHR-01V-A-S
2	ACHR-02V-S
3	ACHR-03V-S
4	ACHR-04V-A-S
5	ACHR-05V-A-S

1

1

2

152.4 +/- 5.0

158.3 +/- 5.0

Electrical Specifications

Current: 2.0A (1~3 circuits) AC/DC

Current: 1.5A (4, 5 circuits) AC/DC

Voltage: 50V AC/DC

SCALE

1: 1

DIMENSIONS

All dimensions are in MM with a tolerance of +/- 3.0 unless otherwise specified.

DRAWN BY

STEVEN PILKINGTON

CHECKED BY

JUSTIN BAKER

CUSTOMER NAME

DESCRIPTION

1.2 mm Pitch ACH Series Standard Leads - 6" Inside Length
DOUBLE-END LEADS

ASSEMBLY PART NO.

ASACHSACH28W152

DRAWING NO. & REVISION

GAM-044

CUSTOMER PART NO.

REVISED

3/7/2016

1	4	3	2	1
1	Add electrical specifications	6/27/2018	SP	
REV.	DESCRIPTION	DATE	BY	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JST:](#)

[ASACHSACH28W152](#)