

4

ITEM	CONNECTOR PART NO.	DESCRIPTION
1	SSHL-002T-P0.2	GH CONNECTOR CONTACT
2	UL1571, 28 AWG	BLACK

3

IPI CHECK

EOR CHECK

2

Applicable Tooling

APPLICATOR

D

C

(314.4 +/- 5.0)

304.8 +/- 5.0

B

A

Applicable Housings

NO. OF CIRCUITS	HOUSING PART NO.
2	GHR-02V-S
3	GHR-03V-S
4	GHR-04V-S
5	GHR-05V-S
6	GHR-06V-S
7	GHR-07V-S
8	GHR-08V-S
9	GHR-09V-S
10	GHR-10V-S
11	GHR-11V-S
12	GHR-12V-S
13	GHR-13V-S
14	GHR-14V-S
15	GHR-15V-S

JST

Electrical Specifications

Current: 1.0A AC/DC

Voltage: 50V AC/DC

SCALE	CUSTOMER NAME	CUSTOMER PART NO.
1: 1		

DIMENSIONS	DESCRIPTION
All dimensions are in MM with a tolerance of +/- 3.0 unless otherwise specified.	1.25 mm Pitch GH Series Standard Leads - 12" Inside Length DOUBLE-END LEADS

DRAWN BY	ASSEMBLY PART NO.
STEVEN PILKINGTON	AGHGH28K305

CHECKED BY	DRAWING NO. & REVISION	REVISED
JUSTIN BAKER	GAM-048	3/7/2016

REV.	DESCRIPTION	DATE	BY
1	Add electrical specifications	6/27/2018	SP

4

3

2

1

Electrical Specifications
Current: 1.0A AC/DC
Voltage: 50V AC/DC

JST

SCALE 1: 1	CUSTOMER NAME	CUSTOMER PART NO.
DIMENSIONS All dimensions are in MM with a tolerance of +/- 3.0 unless otherwise specified.	DESCRIPTION 1.25 mm Pitch GH Series Standard Leads - 12" Inside Length DOUBLE-END LEADS	
DRAWN BY STEVEN PILKINGTON	ASSEMBLY PART NO. AGHGH28K305	
CHECKED BY JUSTIN BAKER	DRAWING NO. & REVISION GAM-048	REVISED 3/7/2016

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JST:](#)

[AGHGH28K152](#)