


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO J.S.T. AND SHALL NOT BE USED OR SHOWN WITHOUT WRITTEN PERMISSION.

1	2	3	4
Item No.	Qty.	Part No.	Description
1	1	SYR-02T	RCY Connector
1	2	SYM-001T-P0.6(N)	RCY Contact
2	207.9 mm	UL1007/1569, 22 AWG	Black
2	207.9 mm	UL1007/1569, 22 AWG	Red

Electrical Specifications
Current: 3.0A AC/DC
Voltage: 250V AC/DC

PIN OUT CHART		
PIN	COLOR	PIN
1	Black	
2	Red	

WIRE CUT LENGTH = 207.9 +/- 5.0



ZONE	REV	DESCRIPTION	DATE	APPROVED
1	1	Add Electrical Specifications	7/02/2018	LM

All dimensions are in millimeters with a default tolerance of +/- 5.0 unless otherwise specified.		CUSTOMER NAME	
		DESCRIPTION	
RCY RECEPTACLE WITH 8" LEADS SEMI-STRIPPED 6.0 MM MATES WITH A02SYR22KR203SS		SIZE	CUSTOMER PART NO.
Drawn By: Larissa Mosley		PART NO.	REV
Checked By: Steven Pilkington		A02SYR22KR203SS	
SCALE 1:1		DRAWING NO. GAM-383	DATE 5/16/2018

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JST:](#)

[A02SYR22KR203SS](#)