


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO J.S.T. AND SHALL NOT BE USED OR SHOWN WITHOUT WRITTEN PERMISSION.

1	2	3	4
Item No.	Qty.	Part No.	Description
1	1	SYP-02T-1	RCY Connector
1	2	SYF-001T-P0.6	RCY Contact
2	258.8 mm	UL1007/1569, 22 AWG	Black
2	258.8 mm	UL1007/1569, 22 AWG	Red

Electrical Specifications
Current: 3.0AAC/DC
Voltage: 250V AC/DC

PIN OUT CHART		
PIN	COLOR	PIN
1	Black	
2	Red	

WIRE CUT LENGTH = 258.8 +/- 5.0



ZONE	REV	DESCRIPTION	DATE	APPROVED
	1	Add Electrical Specifications	7/02/2018	LM

All dimensions are in millimeters with a default tolerance of +/- 5.0 unless otherwise specified.	CUSTOMER NAME	
	DESCRIPTION	
RCY PLUG WITH 10' LEADS SEMI-STRIPPED 6.0 MM MATES WITH A02SYR22KR254SS		
Drawn By: Larissa Mosley	SIZE	CUSTOMER PART NO.
Checked By: Steven Pilkington	SCALE	PART NO.
	1:1	A02SYP22KR254SS
	DRAWING NO. GAM-387	DATE 5/16/2018

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JST:](#)

[A02SYP22KR254SS](#)